

Eaton 012811

Catalog Number: 012811

Eaton Moeller® series DILEM Contactor, 48 V DC, 4 pole, 380 V 400 V, 4 kW, Screw terminals, DC operation

General specifications



Product Name

Eaton Moeller® series DILEM Mini
contactor

Catalog Number

012811

EAN

4015080128113

Product Length/Depth

54 mm

Product Height

58 mm

Product Width

45 mm

Product Weight

0.206 kg

Certifications

IEC/EN 60947-4-1

UL

CSA-C22.2 No. 14-05

CSA

UL 508

CE

IEC/EN 60947

CSA Class No.: 3211-04

UL File No.: E29096

CSA File No.: 012528

UL Category Control No.: NLDX

VDE 0660

Catalog Notes

Also tested according to AC-3e.

Features & Functions

Features

Positive operating contacts to EN 60947-5-1 appendix L, including auxiliary contact module

Number Of Poles

Four-pole

General

Application

Mini Contactors for Motors and Resistive Loads

Lifespan, mechanical

20,000,000 Operations

200,000 Operations (at 240 V, AC-15)

150,000 Operations (at 240 V, DC, L/R = 50 ms: 2 contacts in series 0.5 A)

Mounting position

As required (except vertical with terminals A1/A2 at the bottom)

Operating frequency

9000 mechanical Operations/h

Overvoltage category

III

Pollution degree

3

Product category

Contactors

Protection

Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)

Rated impulse withstand voltage (Uimp)

6000 V AC

Shock resistance

20 g, N/C auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

10 g, N/O main contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

20 g, N/O auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

10 g, N/O main contact, Basic unit without auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

Utilization category

AC-1: Non-inductive or slightly inductive loads, resistance furnaces

AC-3: Normal AC induction motors: starting, switch off during running

AC-4: Normal AC induction motors: starting, plugging, reversing, inching

Voltage type

DC

Climatic environmental conditions

Ambient operating temperature - min

-25 °C

Ambient operating temperature - max

50 °C

Ambient operating temperature (enclosed) - min

25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient storage temperature - min

40 °C

Ambient storage temperature - max

80 °C

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Terminal capacities

Terminal capacity (flexible with ferrule)

1 x (0.75 - 1.5) mm²

2 x (0.75 - 1.5) mm²

Terminal capacity (solid)

1 x (0.75 - 2.5) mm²

2 x (0.75 - 2.5) mm²

Terminal capacity (solid/stranded AWG)

18 - 14

Stripping length (main cable)

8 mm

Screwdriver size

2, Terminal screw, Pozidriv screwdriver

0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver

Tightening torque

1.2 Nm, Screw terminals

Electrical rating

Rated breaking capacity at 220/230 V

90 A

Rated breaking capacity at 380/400 V

90 A

Rated breaking capacity at 500 V

64 A

Rated operational power at AC-3, 240 V, 50 Hz

2.5 kW

Rated operational power at AC-3, 380/400 V, 50 Hz

4 kW

Rated operational power at AC-3, 415 V, 50 Hz

4.3 kW

Rated breaking capacity at 660/690 V

42 A

Rated making capacity up to 440 V (cos phi to IEC/EN 60947)

110 A

Rated operational power at AC-4, 220/230 V, 50 Hz

1.5 kW

Rated operational power at AC-4, 240 V, 50 Hz

1.8 kW

Rated operational power at AC-4, 415 V, 50 Hz

3.1 kW

Rated operational power at AC-4, 440 V, 50 Hz

3.3 kW

Rated operational power at AC-4, 500 V, 50 Hz

3 kW

Rated operational power at AC-4, 660/690 V, 50 Hz

3 kW

Rated operational voltage (Ue) at AC - max

690 V

Rated insulation voltage (Ui)

690 V

Rated operational current (Ie)

0.5 A at 220 V, DC L/R $\leq$ 15 ms (with 3 contacts in series)

2.5 A at 24 V, DC L/R $\leq$ 15 ms (with 1 contact in series)

2.5 A at 60 V, DC L/R $\leq$ 15 ms (with 2 contacts in series)

1.5 A at 100 V, DC L/R $\leq$ 15 ms (with 3 contacts in series)

Rated operational current (Ie) at AC-1, 380 V, 400 V, 415 V

22 A

Rated operational current (Ie) at AC-15, 220 V, 230 V, 240 V

6 A

Rated operational current (Ie) at AC-15, 380 V, 400 V, 415 V

3 A

Rated operational current (Ie) at AC-15, 500 V

1.5 A

Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V

9 A

Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V

9 A

Rated operational current (Ie) at AC-3, 440 V

9 A

Rated operational current (Ie) at AC-3, 500 V

Short-circuit rating

Short-circuit current rating (basic rating)

5 kA, SCCR (UL/CSA)

45 A, max. Fuse, SCCR (UL/CSA)

Short-circuit protection

10 A fast, Max. Fuse 500V, Auxiliary contacts, Short-circuit rating without welding

PKZM0-4, Maximum overcurrent protective device, Short-circuit protection only, Auxiliary contacts, Short-circuit rating without welding

6 A gG/gL, Max. Fuse 500V, Auxiliary contacts, Short-circuit rating without welding

Short-circuit protection rating (type 1 coordination) at 500 V

20 A gG/gL

Short-circuit protection rating (type 2 coordination) at 500 V

10 A gG/gL

Conventional thermal current Ith

Conventional thermal current Ith (1-pole, enclosed)

50 A

Conventional thermal current Ith (3-pole, enclosed)

16 A

Conventional thermal current Ith at 55°C (3-pole, open)

19 A

Conventional thermal current Ith of auxiliary contacts (1-pole, open)

10 A

Conventional thermal current Ith of main contacts (1-pole, open)

60 A

Switching capacity

Switching capacity (main contacts, general use)

15 A, Maximum motor rating (UL/CSA)

Magnet system

Arcing time

12 ms at 690 V AC

6.4 A

Rated operational current (I_e) at AC-3, 660 V, 690 V

4.8 A

Rated operational current (I_e) at AC-4, 220 V, 230 V, 240 V

6.6 A

Rated operational current (I_e) at AC-4, 440 V

6.6 A

Rated operational current (I_e) at AC-4, 500 V

5 A

Rated operational current (I_e) at AC-4, 660 V, 690 V

3.4 A

Rated operational current (I_e) at DC-1, 110 V

20 A

Rated operational current (I_e) at DC-1, 12 V

20 A

Rated operational current (I_e) at DC-1, 220 V

20 A

Rated operational current (I_e) at DC-1, 24 V

20 A

Rated operational current (I_e) at DC-1, 60 V

20 A

Safe isolation

300 V AC, Between coil and contacts, According to EN 61140

300 V AC, Between coil and auxiliary contacts, According to EN 61140

300 V AC, Between the contacts, According to EN 61140

300 V AC, Between auxiliary contacts, According to EN 61140

Changeover time

40 - 50 ms

Duty factor

100 %

Pick-up voltage

0.85 - 1.1 V DC x U_c

Power consumption

Smoothed DC voltage or three-phase bridge rectifier

2.3 VA/W at DC (Pick-up/Sealing power)

Rated control supply voltage (U_s) at AC, 50 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 50 Hz - max

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - max

0 V

Rated control supply voltage (U_s) at DC - min

48 V

Rated control supply voltage (U_s) at DC - max

48 V

Switching time (AC operated, N/O, with auxiliary contact module, closing delay)

70 ms

Switching time (DC operated, make contacts, closing delay) - min

26 ms

Switching time (DC operated, make contacts, closing delay) - max

35 ms

Switching time (DC operated, make contacts, opening delay) - min

15 ms

Switching time (DC operated, make contacts, opening delay) - max

25 ms

Motor rating

Assigned motor power at 115/120 V, 60 Hz, 1-phase

0.5 HP

Contacts

Control circuit reliability

< 2 λ, < 1 failure at 100,000,000 Operations (at U_e = 24 V DC,

Assigned motor power at 200/208 V, 60 Hz, 3-phase

2 HP

Assigned motor power at 230/240 V, 60 Hz, 1-phase

1.5 HP

Assigned motor power at 230/240 V, 60 Hz, 3-phase

3 HP

Assigned motor power at 460/480 V, 60 Hz, 3-phase

5 HP

Assigned motor power at 575/600 V, 60 Hz, 3-phase

5 HP

$U_{min} = 17 \text{ V}$, $I_{min} = 5.4 \text{ mA}$

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Design verification

Equipment heat dissipation, current-dependent P_{vid}

7.17 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

1.79 W

Rated operational current for specified heat dissipation (I_n)

22 A

Static heat dissipation, non-current-dependent P_{vs}

2.3 W

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

Catalogs

Product Range Catalog Switching and protecting motors

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[Switching and protecting motors - catalog](#)

Characteristic curve

[eaton-contactors-short-time-loading-dilm-characteristic-curve.eps](#)

[eaton-contactors-switch-dilm-characteristic-curve.eps](#)

[eaton-contactors-switch-dilm-characteristic-curve-002.eps](#)

[eaton-contactors-component-dilm-characteristic-curve-003.eps](#)

Declarations of conformity

[DA-DC-00004812.pdf](#)

[DA-DC-00004788.pdf](#)

Drawings

[eaton-contactors-diler-dimensions-005.eps](#)

[eaton-contactors-diler-dimensions-004.eps](#)

[eaton-contactors-dilem-dimensions.eps](#)

[eaton-tripping-devices-mounting-diler-contactor-relay-symbol.eps](#)

eCAD model

[ETN.012811.edz](#)

Installation instructions

[IL03407009Z](#)

mCAD model

[DA-CD-dil_em](#)

[DA-CS-dil_em](#)

System overview

[eaton-contactors-accessory-dilem-system-overview.eps](#)

Wiring diagrams

[eaton-contactors-contact-dilem-wiring-diagram.eps](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)