



Figure similar

Pushbutton, 16 mm, round, plastic, blue, pushbutton, raised, 1 NO

<b>product brand name</b>	SIRIUS
<b>product designation</b>	Pushbuttons
<b>design of the product</b>	Complete unit round
<b>product type designation</b>	3SB2
<b>Enclosure</b>	
<b>number of command points</b>	1
<b>Actuator</b>	
<b>design of the actuating element</b>	Pushbutton
<b>principle of operation of the actuating element</b>	momentary contact type
<b>product extension optional light source</b>	No
<b>color of the actuating element</b>	blue
<b>material of the actuating element</b>	plastic
<b>shape of the actuating element</b>	Raised pushbutton
<b>type of unlocking device</b>	without
<b>number of switching positions</b>	2
<b>Front ring</b>	
<b>product component front ring</b>	Yes
<b>design of the front ring</b>	Standard
<b>material of the front ring</b>	plastic
<b>color of the front ring</b>	black
<b>Holder</b>	
<b>material of the holder</b>	Plastic
<b>Contact block/ lampholder</b>	
<b>number of lampholders</b>	0
<b>number of switching elements</b>	1
<b>General technical data</b>	
<b>product function</b>	
• positive opening	No
• EMERGENCY STOP function	No
<b>type of voltage of the operating voltage</b>	AC/DC
<b>protection class IP</b>	IP65
<b>vibration resistance according to IEC 60068-2-6</b>	20 ... 200 Hz: 5g
<b>operating frequency maximum</b>	1 000 1/h
<b>mechanical service life (operating cycles) typical</b>	10 000 000
<b>reference code according to IEC 81346-2</b>	S
<b>Substance Prohibitance (Date)</b>	07/01/2006
<b>Net Weight</b>	0.02 kg
<b>operating voltage rated value</b>	5 ... 250 V

Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	1
number of CO contacts for auxiliary contacts	0
<b>operational current at AC-12</b>	
• at 24 V rated value	10 A
• at 60 V rated value	10 A
• at 110 V rated value	10 A
• at 230 V rated value	10 A
<b>operational current at AC-15</b>	
• at 24 V rated value	4 A
• at 110 V rated value	4 A
• at 230 V rated value	4 A
<b>operational current at DC-12</b>	
• at 24 V rated value	6 A
• at 60 V rated value	5 A
• at 110 V rated value	2.5 A
• at 230 V rated value	1 A
<b>operational current at DC-13</b>	
• at 24 V rated value	3 A
• at 60 V rated value	1.2 A
• at 110 V rated value	0.7 A
• at 230 V rated value	0.3 A

Connections/ Terminals	
type of electrical connection	tab terminals
tightening torque of the screws in the bracket maximum	0.4 N·m

Ambient conditions	
<b>ambient temperature</b>	
• during operation	-25 ... +70 °C
• during storage	-40 ... +80 °C
environmental category during operation according to IEC 60721	3K6

Installation/ mounting/ dimensions	
fastening method	front plate mounting
shape of the installation opening	round
mounting diameter	16 mm
mounting height	12 mm
installation width	19 mm
installation depth	50 mm

Approvals Certificates	
Environment	General Product Approval

[Environmental Confirmations](#)



Test Certificates	
other	

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

[Miscellaneous](#)



[Confirmation](#)

### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2202-0LF01>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2202-0LF01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2202-0LF01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SB2202-0LF01&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2202-0LF01&lang=en)

---

last modified:

4/2/2025 