





FAG

62209-A-2RSR

Deep groove ball bearing

Deep groove ball bearing 622...-A-2RSR,
single row, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	A	Design variant A
Sealing	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	45 mm	Bore diameter
D	85 mm	Outside diameter
B	23 mm	Width
C _r	32,710 N	Basic dynamic load rating, radial
C _{0r}	20,460 N	Basic static load rating, radial
C _{ur}	1,410 N	Fatigue load limit, radial
n _G	4,650 1/min	Limiting speed
≈m	0.489 kg	Weight



Mounting dimensions

$d_{a\ min}$	52 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	78 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	1 mm	Maximum fillet radius

Dimensions

$r_{\min}$	1.1 mm	Minimum chamfer dimension
D_1	72.7 mm	Shoulder diameter outer ring
D_2	76.6 mm	Caliber diameter outer ring
d_1	57.55 mm	Shoulder diameter inner ring
d_2	55 mm	Caliber diameter inner ring

Temperature range

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

Calculation factors

f_0	14.1	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides