

4



3

2

1

LOC G	DIST 02	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C2	ECR-24-230393	21FEB2025	LP	DSC

AMP WIRE RANGE	LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED



- 1 STAMP AMP 22-18* APPROX AS SHOWN
COMMERCIAL WIRE RANGE IS 22-16
- 2 WIRE INSULATION DIAMETER:
ø2.667[.105] TO ø3.556[.140]
- 3 MATERIAL:
BODY & SLEEVE – COPPER PER ASTM B152
INSULATION – PVC
- 4 FINISH:
BODY & SLEEVE– TIN PLATE 0.00254[.000100]
MIN EXT THK PER ASTM B545
INSULATION COLOR – RED
- 5 BODY MATERIAL THK: 0.787±0.051[.031±.002]

1000	LOOSE PIECE	55148-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.26-1.65mm²[509-3260] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 10JUN09	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK TOM MICHIELUTTI 10JUN09				
		APVD TOM MICHIELUTTI 10JUN09	NAME TERMINAL, P.I.D.G., RING TONGUE, BENT 90°, WIRE SIZE: 22-16 AWG			
		PRODUCT SPEC —	—			
		APPLICATION SPEC 114-2157	SIZE A3	CAGE CODE 00779	DRAWING NO C-55148	RESTRICTED TO —
		WEIGHT —				
MATERIAL 3		FINISH 4	CUSTOMER DRAWING			
			SCALE 6:1	SHEET 1 OF 1	REV C2	