

**Product Name // 5mm LED Indicator DX1092 Series**  
**Prominent Profile Black Anodised Aluminium Bezel IP66**  
**Sealed Red/Green/Amber Tri-Colour LED**


[View Product Page](#)


Image not found or type unknown

### // Product Description:

- ⊕ 5mm LED Indicators
- ⊕ Choice of profile, depending on part code prefix:
- ⊕ DX0998, DX1120, DX1090, DX1091: Recessed profile
- ⊕ DX0999, DX1121, DX1092, DX1093: Prominent profile
- ⊕ Choice of Bezel material, depending on part code prefix:
- ⊕ DX0998, DX0999: Chrome Plated Brass
- ⊕ DX1120, DX1121: Glass Filled Nylon
- ⊕ DX1091, DX1093: Anodised Aluminium
- ⊕ DX1090, DX1092: Black Anodised Aluminium
- ⊕ All Aluminium bodied parts are IP66 Front Panel Sealed
- ⊕ Choice of Illumination colour depending on part code:
- ⊕ Single colour LED: /RD - Red, /GN - Green, /YL - Yellow, /BL - Blue
- ⊕ Dual colour LED: /D1 - Red/Green, /D2 - Red/Amber, /D3 - Green/Amber
- ⊕ Tri-colour LED: /TR - Red/Green/Amber
- ⊕ Flashing LED: /RD/02 - Red, /GN/02 - Green
- ⊕ No resistor installed; see data for ratings to enable calculation of suitable series resistor value for application

### // General Information:

Product Display Title:	5mm LED Indicators
Product Family:	Indicators
Product Series:	5mm LED Indicators
Body Material:	Aluminium Black Anodised
Current Max:	0.03A
Diameter:	10.3mm
Function:	LED Indicator
Illumination Colour:	Red/Green/Amber
Illumination Shape:	Dot
Illumination Style:	Illuminated
Illumination Voltage:	No Resistor
Indicator Profile:	Prominent Profile
Ip Rating:	IP66
Max Operating Temperature:	+70°C
Min Operating Temperature:	-40°C
Thread Size:	0.312 inch x 32TPI
Voltage Max:	2.4V

#### // Product PDF Links

[Indicators product data](#)

#### // Product 3D CAD Model Links

[DX1092/TR3D CAD Model](#)