

# Product data sheet

## Subminiature connectors




Product description	<b>M9 Female panel mount connector, Contacts: 4, unshielded, solder, IP67, M12x0.5, Rear mounting</b>
Area	<b>M9 IP67</b>
Series	<b>712</b>
Part no.	<b>09 0412 80 04</b>


### Illustration



### Scale drawing



### Contact arrangement (Plug-in side)



You can find the component part drawing and assembly instructions on the next page.

## Technical data

### General features

Part no.	<b>09 0412 80 04</b>
Connector design	Female panel mount connector
Version	Connector socket straight
Connector locking system	screw
Termination	solder
Degree of protection	IP67
Connection cross-section	0.25 mm <sup>2</sup> / AWG 24
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 500 Mating cycles
Weight (g)	5.37
Customs tariff number	85369010
Country of Origin	DE

### Electrical parameters

Rated voltage	125 V
Rated impulse voltage	1500 V
Rated current	3,0 A
Insulation resistance	≥ 10 <sup>8</sup> Ω
Pollution degree	1
Overvoltage category	II
Insulating material group	III
EMC compliance	unshielded

# Product data sheet

## Subminiature connectors



Product description	<b>M9 Female panel mount connector, Contacts: 4, unshielded, solder, IP67, M12x0.5, Rear mounting</b>
Area	<b>M9 IP67</b>
Series	<b>712</b>
Part no.	<b>09 0412 80 04</b>


### Material

Contact body material	PA (UL94 V-0)
Contact material	CuSn (bronze)
Contact plating	Au (gold)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	e5a54904-12d4-47c9-ba9c-054e5741bc83

### Classifications

eCl@ss 11.1	27-44-01-09
ETIM 9.0	EC003569

### Assembly instructions / Panel cut-out




# Product data sheet

## Subminiature connectors



Product description	<b>M9 Female panel mount connector, Contacts: 4, unshielded, solder, IP67, M12x0.5, Rear mounting</b>
Area	<b>M9 IP67</b>
Series	<b>712</b>
Part no.	<b>09 0412 80 04</b>

### Component part drawing



Product description	<b>M9 Female panel mount connector, Contacts: 4, unshielded, solder, IP67, M12x0.5, Rear mounting</b>
Area	<b>M9 IP67</b>
Series	<b>712</b>
Part no.	<b>09 0412 80 04</b>

### **General Disclaim Notice**

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.