

# Eaton EBH113TBV1

Catalog Number: EBH113TBV1

Eaton Bussmann series low voltage NH fuse base, Switch disconnecter, low voltage, 250 A, AC 690 V, NH1, AC23B, 3P, IEC, 60mm busbar, bottom cable terminals for connection of sector-shaped conductors - V-clamps



## General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH fuse base	EBH113TBV1
	EAN
	5027590336086
Product Length/Depth	Product Height
280 mm	170 mm
Product Width	Product Weight
190 mm	3004 g
Compliances	Certifications
CE	IEC/EN 60947-1
	IEC 60947-3

## Product specifications

### Type

Fuse accessory

### Application

Motor control centres, distribution boards, Cable distribution cabinets

### Amperage Rating

250 A

### Rated operational power at AC-23A, 400 V, 50 Hz

0.1 kW

### Rated permanent current (Iu)

250 A

### Rated uninterrupted current (Iu)

250 A

### Conditioned rated short-circuit current Iq

0.08 kA

### With error protection

No

### Number of poles

Three-pole

### Rated operation power at AC-23, 400 V

0.1 kW

### Rated short-time withstand current (Icw)

80 A

### Electrical connection type of main circuit

Cable clamp

### Actuator position

Front side

### Actuator type

Cover grip

### Construction size

NH1

### Fuse shape

Horizontal

### Suitable for

Busbar mounting

## Resources

### Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[CA134002EN](#)

### Declarations of conformity

[UKCA fuse switch disconnectors, EBC, EBV and EBH series](#)

[CE fuse switch disconnectors, EBC, EBV and EBH series](#)

### Technical data sheets

[10275 EBV Vertical fuse switch-disconnector](#)

### Technical service bulletins

[10293 EBH Horizontal switch-disconnector](#)

NH1

Suitable for fuses

NH1

Cable entry type

Bottom

Mounting method

60 mm busbar mounting

100 mm busbar mounting

Mounting plate

Voltage rating

690

Degree of protection (front side)

IP30

Electrical connection type

Cable clamp

Rated operating voltage (Ue) at AC - max

690 V



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)