
ALMD-LG37, ALMD-LL37, ALMD-LM37, ALMD-LB37

High Brightness SMT Oval LED Lamps Amber, Red, Green and Blue



Data Sheet



Description

The new Avago ALMD-Lx37 Oval LED series has the same or just slightly less luminous intensity than conventional high brightness through holes LEDs.

The new Oval LED lamps can be assembled using common SMT assembly processes and are compatible with industrial reflow soldering processes.

The LEDs are made with an advanced optical grade epoxy for superior performance in outdoor sign applications. The surface mount Oval LEDs are specifically designed for full color / video signs and indoor or outdoor passenger information sign applications.


For easy pick and place assembly, the LEDs are shipped in tape and reel. Every reeled is shipped from a single intensity and color bin except the red color for better uniformity.

Features

- Well defined spatial radiation pattern
- High brightness material
- Available in Red, Amber, Green and Blue color:
 - Red AllnGaP 626 nm
 - Amber AllnGaP 590 nm
 - Green InGaN 525 nm
 - Blue InGaN 470 nm
- JEDEC MSL 2A
- Compatible with reflow soldering process
- Tinted and diffused lens
- Wide viewing angle: 40° x 100°

Applications

- Full color signs
- Mono color signs



CAUTION: InGaN devices are Class 1C HBM ESD sensitive, AllnGaP devices are Class 1B ESD sensitive per JEDEC Standard. Please observe appropriate precautions during handling and processing. Refer to Application Note AN-1142 for additional details.

CAUTION: Customer is advised to always keep the LED in the moisture barrier bag with <5%RH when not in use as prolonged exposure to environment might cause the leads to tarnish or rust, which might cause difficulties in soldering.

Package Dimensions

Device Selection Guide

Part Number	Color and Dominant Wavelength	Luminous Inte	Viewing Angle	
	$\lambda_{ m d}$ (nm) Typ	Min	Мах	Typ - ° ^[4]
ALMD-LG37-XZ002	Red 626	1660	2900	40° x 100°
ALMD-LL37-XZ002	Amber 590	1660	2900	40° x 100°
ALMD-LM37-24002	Green 525	3500	6050	40° x 100°
ALMD-LB37-SU002	Blue 470	660	1150	40° x 100°

Notes:

1. The luminous intensity is measured on the mechanical axis of the lamp package and it is tested with pulsing condition.


2. The optical axis is closely aligned with the package mechanical axis.

3. Dominant wavelength, Ad, is derived from the CIE Chromaticity Diagram and represents the color of the lamp.

4. θ ¹/₂ is the off-axis angle where the luminous intensity is half the on-axis intensity.

5. Tolerance for each bin limit is $\pm 15\%$

Part Numbering System



Absolute Maximum Rating, $T_J = 25 \ ^\circ C$

Parameter	Red and Amber	Green	Blue	Unit
DC Forward Current ^[1]	50	30	20	mA
Peak Forward Current	100 [2]	100 [3]	100 [3]	mA
Power Dissipation	120	114	76	mW
LED Junction Temperature		110		°C
Operating Temperature Range		-40 to +85		°C
Storage Temperature Range		-40 to +100		°C

Notes:

1. Derate linearly as shown in Figure 4 and Figure 9.

2. Duty Factor 30%, frequency 1kHz.

3. Duty Factor 10%, frequency 1kHz.

Electrical / Optical Characteristics, $T_J = 25 \degree C$

Parameter	Symbol	Min.	Тур.	Max.	Units	Test Conditions
Forward Voltage	V _F				V	$I_F = 20 \text{ mA}$
Red		1.8	2.1	2.4		
Amber		1.8	2.1	2.4		
Green		2.8	3.2	3.8		
Blue		2.8	3.2	3.8		
Reverse Voltage [3]	V _R					
Red & Amber		5			V	$I_{R} = 100 \mu A$
Green & Blue		5				$I_R = 10 \ \mu A$
Dominant Wavelength [1]	λ_d					$I_F = 20 \text{ mA}$
Red		618.0	626.0	630.0		
Amber		584.5	590.0	594.5		
Green		519.0	530.0	539.0		
Blue		460.0	470.0	480.0		
Peak Wavelength						
Red	λ_{PEAK}		634		nm	Peak of Wavelength of Spectral
Amber			594			Distribution at $I_F = 20 \text{ mA}$
Green			516			
Blue			464			
Thermal Resistance	Rθ _{J-PIN}				°C/W	LED Junction-to-Pin
Red			270			
Amber			270			
Green			270			
Blue			480			
Luminous Efficacy ^[2]						
Red	η_V		200		lm/W	Emitted Luminous Power/Emitted
Amber			490			Radiant Power
Green			530			
Blue			65			
Thermal coefficient of λ_d					nm/°C	$I_F = 20 \text{ mA}$; +25°C $\leq T_J \leq +100$ °C
Red			0.059			
Amber			0.103			
Green			0.028			
Blue			0.024			

Notes:

1. The dominant wavelength is derived from the chromaticity Diagram and represents the color of the lamp.

2. The radiant intensity, le in watts per steradian, may be found from the equation $le = l_V/\eta_V$ where l_V is the luminous intensity in candelas and η_V is the luminous efficacy in lumens/watt.

3. Indicates product final testing condition. Long term reverse bias is not recommended.






Figure 1. Relative Intensity vs Wavelength




Figure 2. Forward Current vs Forward Voltage




Figure 3. Relative Intensity vs Forward Current




Figure 5. Relative Dominant Wavelength Shift vs Forward Current





Figure 4. Maximum Forward Current vs Ambient Temperature








Figure 7. Forward Current vs Forward Voltage




Figure 8. Relative Intensity vs Forward Current




Figure 10. Dominant Wavelength Shift vs Forward Current




Figure 9. Maximum Forward Current vs Ambient Temperature

InGaN




Figure 11a. Radiation Pattern for Major Axis




Figure 11b. Radiation Pattern for Minor Axis




Figure 12. Relative Intensity Shift vs Junction Temperature







Figure 13. Forward Voltage Shift vs Junction Temperature



Note: Recommended stencil thickness is 0.1524mm (6 mils) minimum and above





10 to 30 SEC.

°C/SEC. MAX.

100 SEC. MAX.

Note:

1. Nozzle depth should be touching LED flange during pick and place.

2. Nozzle width should be able to fit into LED carrier tape.






Figure 16. Recommended Leaded Reflow Soldering Profile

Figure 17. Recommended Pb- Free Reflow Soldering Profile

TIME

Note: For detailed information on reflow soldering of Avago Surface Mount LED, refer to Avago Application Note AN1060 Surface Mounting SMT LED Indicator Components.




Figure 18. Carrier Tape Dimension




Figure 19. Reel Dimension




Figure 20. Unit Orientation from reel

Intensity Bin Limit Table (1.2:1 lv bin ratio)

	Intensity (mcd) at 20 mA				
Bin	Min	Мах			
S	660	800			
Т	800	960			
U	960	1150			
V	1150	1380			
W	1380	1660			
Х	1660	1990			
Y	1990	2400			
Z	2400	2900			
1	2900	3500			
2	3500	4200			
3	4200	5040			
4	5040	6050			

VF Bin Table (V at 20 mA) for Red & Amber

Bin ID	Min	Мах
VD	1.8	2.0
VA	2.0	2.2
VB	2.2	2.4

Tolerance for each bin limit is $\pm 0.05V$

Tolerance for each bin limit is $\pm 15\%$

Red Color Range

Min Dom	Max Dom	Xmin	Ymin	Xmax	Ymax
618.0	630.0	0.6872	0.3126	0.6890	0.2943
		0.6690	0.3149	0.7080	0.2920

Tolerance for each bin limit is $\pm\,0.5$ nm

Amber Color Range

	Min	Мах				
Bin	Dom	Dom	Xmin	Ymin	Xmax	Ymax
1	584.5	587.0	0.5420	0.4580	0.5530	0.4400
			0.5370	0.4550	0.5570	0.4420
2	587.0	589.5	0.5570	0.4420	0.5670	0.4250
			0.5530	0.4400	0.5720	0.4270
4	589.5	592.0	0.5720	0.4270	0.5820	0.4110
			0.5670	0.4250	0.5870	0.4130
6	592.0	594.5	0.5870	0.4130	0.5950	0.3980
			0.5820	0.4110	0.6000	0.3990

Tolerance for each bin limit is \pm 0.5 nm

Green Color Range

Bin	Min Dom	Max Dom	Xmin	Ymin	Xmax	Ymax
1	519.0	523.0	0.0667	0.8323	0.1450	0.7319
			0.1200	0.7375	0.0979	0.8316
2	523.0	527.0	0.0979	0.8316	0.1711	0.7218
			0.1450	0.7319	0.1305	0.8189
3	527.0	531.0	0.1305	0.8189	0.1967	0.7077
			0.1711	0.7218	0.1625	0.8012
4	531.0	535.0	0.1625	0.8012	0.2210	0.6920
			0.1967	0.7077	0.1929	0.7816
5	535.0	539.0	0.1929	0.7816	0.2445	0.6747
			0.2210	0.6920	0.2233	0.7600

Tolerance for each bin limit is \pm 0.5 nm

Blue Color Range

	Min	Мах				
Bin	Dom	Dom	Xmin	Ymin	Xmax	Ymax
1	460.0	464.0	0.1440	0.0297	0.1766	0.0966
			0.1818	0.0904	0.1374	0.0374
2	464.0	468.0	0.1374	0.0374	0.1699	0.1062
			0.1766	0.0966	0.1291	0.0495
3	468.0	472.0	0.1291	0.0495	0.1616	0.1209
			0.1699	0.1062	0.1187	0.0671
4	472.0	476.0	0.1187	0.0671	0.1517	0.1423
			0.1616	0.1209	0.1063	0.0945
5	476.0	480.0	0.1063	0.0945	0.1397	0.1728
			0.1517	0.1423	0.0913	0.1327


Tolerance for each bin limit is \pm 0.5 nm

Packing Label

(i) Mother Label (Available on MBB bag)



(ii) Baby Label (Available on Plastic Reel)



Note: Acronyms and Definition:

BIN:

(i) Color bin only or VF bin only


(Applicable for part number with color bins but without VF bin OR part number with VF bins and no color bin)

(ii) Color bin incorporated with VF bin

Applicable for part number that have both color bin and VF bin

Example:

- a. Color bin only or VF bin only
 BIN: 4 (represent color bin 4 only)
 BIN: VA (represent VF bin "VA" only)
- b. Color bin incorporate with VF bin



Handling of Moisture Sensitive Device

This product has a Moisture Sensitive Level 2a rating per JEDEC J-STD-020. Refer to Avago Application Note AN5305, Handling of Moisture Sensitive Surface Mount Devices, for additional details and a review of proper handling procedures.

A. Storage before use

- An unopened moisture barrier bag (MBB) can be stored at < 40 °C/90% RH for 12 months. If the actual shelf life has exceeded 12 months and the humidity indicator card (HIC) indicates that baking is not required then it is safe to reflow solder the LEDs per the original MSL rating.
- It is recommended that the MBB not be opened prior to assembly (e.g., for IQC).

B. Control after opening the MBB

- The humidity indicator card (HIC) shall be read immediately upon opening of the MBB.
- The LEDs must be kept at < 30 °C/60% RH at all times, and all high temperature related processes including soldering, curing or rework need to be completed within 672 hours.

C. Control for unfinished tape and reel parts

• Unused LEDs must be stored in a sealed MBB with a desiccant or desiccator at < 5% RH.

D. Control of assembled boards

 If the PCB soldered with the LEDs is to be subjected to other high temperature processes, the PCB needs to be stored in a sealed MBB with desiccant or desiccator at < 5% RH to ensure that all LEDs have not exceeded their floor life of 672 hours

E. Baking is required if:

- The HIC indicator is not BROWN at 10% and is AZURE at 5%
- The LEDs are exposed to a condition of > 30 ° C/60% RH at any time.
- The LED floor life exceeded 672 hours.

The recommended baking condition is: 60 ± 5 °C for 20 hours.

DISCLAIMER: Avago's products and software are not specifically designed, manufactured or authorized for sale as parts, components or assemblies for the planning, construction, maintenenace or direct operation of a nuclear facility or for use in medical devices or applications. Customer is solely responsible, and waives all rights to make claims against avago or its suppliers, for all loss, damage, expense or liability in connection with such use.

For product information and a complete list of distributors, please go to our web site: www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries. Data subject to change. Copyright © 2005-2014 Avago Technologies. All rights reserved. AV02-4541EN - September 8, 2014

