


KEMET Part Number: ALC70C132FP550
(A546JW132M550C)

ALC70, Aluminum Electrolytic, 1,300 uF, 20%, 550 VDC, -40/+85°C



General Information

Supplier:	KEMET
Series:	ALC70
Dielectric:	Aluminum Electrolytic
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	4 Pin
AEC-Q200:	No
Notes:	Dimensions D And L Include Sleaving
Shelf Life:	156 Weeks

Dimensions

D	45mm +1mm
L	105mm +/-2mm
S	22.5mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications

Weight:	225 g
Sleaving:	Yes
Packaging:	Bulk, Bag

Specifications

Capacitance:	1,300 uF
Capacitance Tolerance:	20%
Voltage DC:	550 VDC, 605 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage at 85C)
Resistance:	316 mOhms (100Hz 20C), 273 mOhms (10kHz 20C)
Ripple Current:	5.12 Amps (100Hz 85C), 7.94 Amps (10kHz 85C)
Leakage Current:	4290 uA (5min 20°C)