FLUX[™]



A lightweight modern safety spectacle featuring a soft brow-pad to allow greater protection against dust and droplets. The wraparound lens offers a large field of vision with added comfort from the soft injected nose piece and temple.

SPECIAL FEATURES

- Single wraparound polycarbonate lens
- Soft, adjustable anti-slip nose bridge
- Soft brow-pad further protects eyes against dust and droplet
- Co-injected bi-colour thermoplastic rubber temples provide a secure fit
- Multi-functional for a personalised fit: 3-position length adjustable temples and lens inclination adjustment







VERSION	IS	REF.	LENS MARKING	FRAME MARKING	PROTECTION AGAINST	COATINGS
CLEAR	0	RLY00481	2C-1.2 € 1FTKN € € / Z87+U6	€ EN 166 FT C € / Z87+	Impacts, UV radiations	
GREY		RLY00482	5-2.5 € 1FTKN C€/Z87+ U6 L2.5	€ EN 166 FT C € / Z87+	Impacts, UV radiations	K&N Anti-scratch and Anti-fog
BLUE		RLY00483	2C-1.2 € 1FTKN € € / Z87+U6	€ EN 166 FT (€ / Z87+	Impacts, UV radiations	- / UV400 / Moisture repellent
INDOOR OUTDOO	OR ①	RLY00484	5-1.7 € 1FT C € / Z87+ U6 L1.7	€ EN 166 FT C € / Z87+	Impacts, UV radiations	▲ ARIDA Moisture Repellent + Anti-fog

See overleaf for this product's technical specification>



GENERAL SPECIFICATION

LENS BASE	9mm	
WEIGHT	24g	

PACKAGING

Individually contained in a polythene bag with a Euroslot

PER BOX	10
PER CARTON	200

COMPONENT SPECIFICATION

COMPONENT	MATERIAL	FEATURES	
LENS	Polycarbonate	Comfortable and flexible	
NOSE BRIDGE	Thermoplastic Elastomers (TPE)	Co-injected - Durable and flexible, with secure and comfortable grip	
TEMPLE	TR90 Thermoplastic / Thermoplastic Elastomers (TPE)	Increased flexibility and strength	
HINGE	TR90 Thermoplastic / Metal	Integrated brow-pad	

LENS MARKINGS (CE)

LENS FILTER TYPE:

2C UV

5 Solar

SCALE NUMBER (SHADE):

1.2 Clear or Amber

1.7 Minimises or I/O

2.5 Grey or Revo

@ Identity of manufacturer

OPTICAL CLASS:

1 High optical quality

MECHANICAL STRENGTH:

Low energy impact, resists a 6mm, 0.86g ball at 45m/s

Protection against high-speed particles at extreme temperatures

PERFORMANCE:

K Resistance to scratches by fine particles

N Resistance to fogging

C€ Certification mark

FRAME MARKINGS

C Identity of manufacturer

EN 166: guaranteed minimum resistance of the protective eyewear against everyday risks including dropping the protective eyewear onto the ground, ageing by light exposure, exposure to heat or corrosion etc.

MECHANICAL STRENGTH:

Low energy impact, resists a 6mm, 0.86 g ball at 45m/s

T Protection against high-speed particles at extreme temperatures

C€ Certification mark

USA (ANSI)

LENS

U6 UV (Clear, Amber, Blue) L1.7 Solar (I/O, Twilight) L2.5 Solar (Grev)

LENS AND FRAME:

Z87+ High velocity impact, 0.25 inch, 1.04g ball at 150ft/s

CLEANING AND STORAGE

CLEANING: The lenses should be cleaned regularly.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the

complete product. After each use it is recommended to keep the spectacles or goggles in a microfibre pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.

PART OF THE GLOBUS GROUP

Based on a substantial heritage of successfully protecting hands, Globus has grown to become one of the world leaders in worker safety, leading the way in technical innovation to provide a range of products that have set the standard for safety, productivity and wearer acceptance.

This focus on creating cutting edge personal protection solutions has now extended to eye and face protection with Riley; a new collection of high performance protective eyewear products engineered with innovation and ingenuity, designed for optimum comfort and styled for safe working.

Riley product approval certificates to CE standards will be provided on request. Riley is a registered trademark.

www.riley-eyewear.com

E: info@riley-eyewear.com T: +44 (0)161 877 4747

F: +44(0)161 877 4746

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, United Kingdom

