



PLUG-IN RELAY COMPACT UNIT DC 24V,
2 CO CONTACT LED MODULE RED STANDARD PLUG-IN
SOCKET SCREW TERMINAL

General technical details:

type of voltage		DC
Control supply voltage		
• for DC / rated value		
• minimum	V	24
• maximum	V	24
Number of NC contacts		
• for auxiliary contacts		0
Number of NO contacts		
• for auxiliary contacts		0
Number of change-over switches		
• for auxiliary contacts		2
Operating current / of the auxiliary contacts		
• at AC-15		
• at 230 V	A	2.5
Design of the switching function		
• guided		changeover switch No
Switching behaviour		monostable

Mechanical design:

Design of the electrical connection	screw-type terminals
--	----------------------

Design of the relay operating mechanism		poled
Product component / jumper socket		Yes
Width	mm	15.5
Height	mm	71
Depth	mm	78

Certificates/approvals:

General Product Approval

other



GOST

[Declaration of Conformity](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

CAX-Online-Generator

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/LZS:RT4A4L24/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=LZS:RT4A4L24

last change:

Oct 24, 2011