

## FEATURES

- **LED bulb type:** Offers energy efficiency and long-lasting performance
- **Flashing light effect:** Ensures high visibility in alert situations
- **Sound level up to 92 dB:** Provides a clear and effective audible warning
- **IP43 rating:** Suitable for indoor use, protecting against solid objects over 1mm and water spray
- **ABS housing material:** Durable and resistant to impact, ensuring longevity
- **Operating temperature range -20 °C to 50 °C:** Reliable performance in diverse environmental conditions
- **DC current type:** Compatible with 24 V DC power systems
- **Screw mount type:** Easy installation and secure attachment

## RS PRO LED Horn-Beacon Combination, 24 V DC

RS Stock No: 658-304



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO Horn-Beacon Combination is a versatile signalling device designed for industrial environments. It combines both visual and audible alerts, making it ideal for situations where clear and immediate notification is required. The unit is particularly beneficial in noisy settings where visual signals are necessary to ensure safety and compliance.

## General Specifications

Bulb Type	LED
Housing Colour	Grey
Lens Colour	Red
Light Effect	Flashing
Mount Type	Screw
Number of Tones	1
Product Type	Horn-Beacon Combination
Sounder Type	Sounder Beacon

## Electrical Specifications

Current Consumption	0.32 A
Current Type	DC
Maximum Supply Voltage	24 V dc

## Mechanical Specifications

Housing Material	ABS
------------------	-----

## Protection Category

IP Rating	IP43
-----------	------

## Operation Environment Specifications

Maximum Operating Temperature	50 °C
Minimum Operating Temperature	-20 °C

## Measurement Specifications

Maximum Sound Level	92 dB
Minimum Sound Level	88 dB

## Approvals

Standards/Approvals	CE, EAC
---------------------	---------