

Vacuum Cleaner XGT®, VC013GL

40Vmax, 150 mbar, 7.5 L, Class L

Model VC013GL is a vacuum cleaner powered by a 40VMax XGT Li-Ion battery.

Enhanced suction power and low noise level.
Features and benefits: Auto-start Wireless system (AWS). Dust type: Wet & Dry. Variable suction power control. Tank capacity: 7.5L for Dry, 4.5L for Wet



Technical specifications

Vacuum hose length	0,5 - 2,0 m
Vacuum hose diameter	28 mm
Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	2,0 m³/min
Max. sealed suction	150 mbar
Suction power	165 W
Automatic Filter Cleaning System	✓
AWS ready	✓
Continuous use XGT® 40Vmax / 5.0 Ah	22 - 120 min
Tank Capacity for Dust	7,5 L
Tank Capacity for Liquids	4,5 L
Sound Pressure Level (L _{pA})	75 dB(A)
Product net weight	4,3 kg
Noise Uncertainty (K Factor)	2,5 dB(A)

User benefits

- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- Variable suction power control by dial
- For both wet and dry vacuum cleaning
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Battery level indicator
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing