

FEATURES

- Universal 85 305Vac and 120 -430Vdc
- Active PFC
- Remote ON-OFF
- Operating temperature range
 30°C to +70°C
- Output short circuit, over-current (Built-in constant current limiting circuit), over-voltage, overtemperature protection.
- EMI performance meets.
 CISPR32 / EN55032 CLASS B
- Safety EN/UL/IEC 62368 IEC/EN60335-1, GB4943-1
- Over-voltage class III
- Operating Altitude upto 5000m
- Supplied with Terminal cover

RS PRO Embedded Switch Mode Power Supplies

- 2193029
- 2193030
- 2193032



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

AC-DC switching power supply with built-in active PFC function. Provides high efficiency and high reliability solutions for industrial, street lighting and instrumentation applications. These converters offer excellent EMC performance, meeting CISPR32/EN55032 Class B and IEC/EN61000-4. Safety approval UL/EN/IEC62368, EN60335, GB4943

Model	AC-DC Enclosed 150W
Mounting Type	Chassis Mount
MTBF	MIL-HDBK-217F@25°C > 300,000 h
Applications	Industrial control systems, instrumentation and lighting

RS Stock#	Input Voltage	Output Voltage	Output Current	Adj' range (V)	Wattage	Efficiency (Typ)
2193029	85 to 305V ac 120 to 430V dc	12V DC	12.5A	10.2-13.8V	150W	85.5%
2193030	85 to 305V ac 120 to 430V dc	24V DC	6.3A	21.6-28.8V	151W	87%
2193032	85 to 305V ac 120 to 430V dc	48V DC	3.2A	45.6-55.2V	153W	88%

Input Specifications

Item	Operating Condit	Min	Тур	Max.	Unit	
Innut Valtaga Banga	AC Input		85	-	305	VAC
Input Voltage Range	DC Input		120	-	430	VDC
Input Voltage Frequency			47	-	63	Hz
Input Current	115VAC 230VAC		-	-	2	•
			-	-	1	
Inrush Current	115VAC	Cald Chart	-	-	30	Α
	230VAC	Cold Start	-	-	45	
Power Factor	115VAC	At full Load	0.97	0.99	-	
	230VAC		0.91	0.98	-	
Leakage Current	277VAC			<2	:mA	
Hot Plug			Unava	ailable		



Output Specifications

Item	Operating Conditions			Min	Тур	Max.	Unit
Output Voltage Accuracy	Full Load Range 12V		-	±2	-		
		24V/48V		-	±1	-	
Line Regulation	Rated Load			-	±0.5	-	%
Load Regulation	0% - 100% load			-	±0.5	-	
Output Ripple & Noise*	20MHz bandwidth	ı	12V	-	100	-	mV
	(peak-to-peak valu	ue)	24V	-	150	-	
			48V	-	200	-	
Temperature Coefficient				-	±0.05	-	%/°C
Minimum Load				0	-	-	%
Hold-up Time	230VAC			16	-	-	ms
Short Circuit Protection	Recovery time <3s after the short		Constant current, continuous, self-				
	circuit disappear			recover			
Over-current Protection			105%-150 self-recov	50% Io, constant current mode,			
	12V 24V			≤ 16.8V (Output voltage turn off, re-			
			power on for recover)				
			≤ 33.6V(Output voltage turn off, re-				
Over-voltage Protection			power on for recover)				
	48V		≤ 60V (Output voltage turn off, re-power				
	40 V	V		on for red	on for recover)		
Over-temperature	Over-temperature Protection Activation		-	-	85	°C	
Protection*	Over-temperature Protection Deactivation			50	-	-	, t
Remote Control	Open or 0~0.8VDC Power ON		0	-	0.8	VDC	
	4-10VDC Power OFF		4	-	10	VDC	

Note: *The "Tip and barrel method" is used for ripple and noise test, output parallel 47uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to Enclosed Switching Power Supply Application Notes for specific information. *Over-temperature Protection needs to be tested under rated full load conditions.



General Specifications

Item		Operating Conditions	Min	Тур	Max.	Unit	
Input-Earth		Electric Strength Test for 1min, leakage current <10mA	2000	-	-		
Isolation Input-o	Input-output	Electric Strength Test for 1min, leakage current <10mA	4000	-	-	VAC	
Output-Earth		Electric Strength Test for 1min, leakage current <5mA		-	-		
la a clatia a	Input-Earth	500VDC, 25±5°C,	100	-	-		
Insulation	Input-output	Humidity < 95%RH, non-	100	-	-	МΩ	
Resistance	Output-Earth			-	-		
Operating Temperature			-30	-	+70	°C	
Storage Temperature			-40	-	+85	٠,	
Storage Humidity		Non-condensing	10	-	95	%RH	
Power Derating		+50°C to +70°C	2	-	-	0/ /0C	
		-30°C to -20°C	4	-	-	%/°C	
		85VAC-100VAC	1.3	-	-	%/VAC	
		2000m-5000m	5	-	-	%/m	
Altitude			-	-	5000	m	
Safety Certification UL/EN/IEC62368/EN60335/			GB4943				
Safety Class	afety Class CLASS I						
MTBF MIL-HDBK-217F@25°C >300,000 h			0,000 h				

EMC Specifications


Emissions	CE	CISPR32/EN55032 CLASS B	
	RE	CISPR32/EN55032 CLASS B	
	Harmonic Current	IEC/EN61000-3-2 CLASS D	
	Voltage Flicker	IEC/EN61000-3-3	
Immunity	ESD	IEC/EN 61000-4-2 Contact ±6KV /Air ±8KV	Perf. Criteria A
•	RS	IEC/EN 61000-4-3 10V/m	Perf. Criteria B
	EFT	IEC/EN 61000-4-4 ±2KV	Perf. Criteria A
	Surge	IEC/EN 61000-4-5 ±1KV/±2KV	Perf. Criteria A
	CS	IEC/EN61000-4-6 10 Vrms	Perf. Criteria A
	DIP (AC input)	IEC/EN61000-4-11 0%, 70%	Perf. Criteria B

Mechanical Specifications



Case Material	Metal (AL1100, SGCC)		
Dimensions	179 x 99 x 30.0mm		
Weight	500g (Typ.)		
Cooling Method	Free air convection		

Dimensions and recommended layout







Approvals


Safety Standard	Meet UL/EN/IEC62368/EN60335/GB4943		
Safety Certification	UL/EN/IEC62368/EN60335/GB4943		
Safety Class	Class I (PE and must be connected)		

Product Characteric Curve



Note: U With an input voltage between 85-100VAC and a DC input between 120-140VDC the output power must be derated as per the temperature derating curves;





Note:



- 1. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity.
- 2. All index testing methods in this datasheet are based on our company corporate standards.
- 3. To improve the efficiency at high input voltage, there will be audible noise generated, but it does not affect product performance and reliability.
- 4. Products are related to laws and regulations: see "Features" and "EMC".
- 5. The out case needs to be connected to PE of system when the terminal equipment in operating.
- 6. Our products shall be classified according to ISO14001 and related environmental laws and regulations and shall be handled by qualified units.
- 7. The power supply is considered a component which will be installed into a terminal equipment. All EMC tests should be confirmed with the final equipment.