


Geberit Mapress Carbon Steel bend



Example image



APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For extinguishing water (wet)
- For sprinklers (wet)
- For compressed air (oil purity class 3)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Outside zinc-plated
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material Non-alloy steel 1.0034 E195 (EN 10305)

INFO

- Dimension changes of individual articles as per table will be completed by end of May 2026

Art. no.	DN	d, ø mm	arc °	L cm	Z cm
20601	10	12	45	3.2	1.5
20602	12	15	45	3.6	1.6
20603	15	18	45	3.7	1.7
20604	20	22	45	4.2	2.1

Art. no.	DN	d, ø mm	arc °	L cm	Z cm
20605	25	28	45	4.8	2.5
23606	32	35	45	4.3	1.7
23607	40	42	45	5.1	2.1
23608	50	54	45	6.2	2.7
20612	65	66.7	45	9.3	4.2
20609	65	76.1	45	10.3	5
20610	80	88.9	45	11.7	5.7
20611	100	108	45	14.3	6.8
20101	10	12	90	4.2	2.5
20102	12	15	90	4.9	2.9
20103	15	18	90	5.3	3.3
20104	20	22	90	6.1	4
20105	25	28	90	7.2	4.9

<i>Art. no.</i>	<i>DN</i>	<i>d_ø mm</i>	<i>arc °</i>	<i>L cm</i>	<i>z cm</i>
23106	32	35	90	6.8	4.2
23107	40	42	90	8	5
23108	50	54	90	10	6.5
20112	65	66.7	90	14.1	9.1
20109	65	76.1	90	15.7	10.4
20110	80	88.9	90	18.4	12.4
20111	100	108	90	22.6	15.1