




Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**  
Insertion & Extraction Tool Application: **Contact-to-Wire**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Wire

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (2.58% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability
















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 <p>TE Part # 962953-1 4MM SOCKET CONTACT SWS LOOSE PIECE</p>	 <p>TE Part # 962957-1 4MM BU-KONTAKT EDS</p>	 <p>TE Part # 962955-1 4MM SOCK.CONT.(LP)</p>	 <p>TE Part # 965840-1 4MM BUCHSENKONTAKT</p>
 <p>TE Part # 1703420-2 DIA 4MM CON</p>	 <p>TE Part # 962955-5 4MM BUCHS-KONTAKT</p>	 <p>TE Part # 6-962952-6 4MM BUCHS-KONTAKT</p>	 <p>TE Part # 3-965867-1 ABS4MM BU REPAR-KIT</p>
 <p>TE Part # 1703420-5 DIA 4MM CON</p>	 <p>TE Part # CAT-R7602-T273 ROUND CONNECTOR SYSTEM, PIN AND SOCKET</p>	 <p>TE Part # 962955-2 4MM RECEPTACLE CONTACT SWS (1,0-2,5MM?)</p>	 <p>TE Part # 965868-1 4MM SOCKET CONTACT</p>
 <p>TE Part # 962953-2 4MM SOCKET CONTACT SWS</p>	 <p>TE Part # 962957-2 4MM BU-KONTAKT EDS</p>	 <p>TE Part # 965867-1 4MM SOCKET CONTACT</p>	


Also in the Series | Round Connector System



Automotive Connector Caps & Covers (5)



Automotive Housings(12)



Automotive Terminals(48)



Connector Seals & Cavity Plugs(5)



DIN Connectors(3)



Insertion & Extraction Tools(8)

Customers Also Bought




TE Part #1-1579008-8  
EXTRACTION TOOL




TE Part #CAT-T3437-ST2999  
STD Snap-On Markers



TE Part #CAT-C73765-M1E  
M12 Field Installable Unshielded



TE Part #1804030-1  
EXTRACTION TOOL ASSY



TE Part #4-1473562-4  
RITS CONN. PLUG ASSY 4P GREEN



TE Part #130046  
PIDG RING TONGUE



TE Part #DT04-3P-EP10  
REC, 3P, BLK, 120 OHM RESISTOR



TE Part #2-1579008-3  
EXTRACTION TOOL

Documents

Datasheets & Catalog Pages  
CRIMPING TERMINALS

English

CRIMPING WHERE FORM MEETS FUNCTION

English