


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-	A	INITIAL RELEASE	16OCT2009	RC AH



NOTES:

- 1 ATTENUATION ≤ 0.3 dB, MEASURED AT 1310 nm ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2 RETURN LOSS ≥ 45 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 1310 nm
- 3 TUNED CONNECTORS
- 4 CABLE INFORMATION:
 - CORE DIAMETER: 9/125 μ m
 - OUTER JACKET DIAMETER: 2.0 mm
 - OUTER JACKET COLOUR: YELLOW
 - OUTER JACKET MATERIAL: LSZH
- 5 INFORMATION ON LABEL
 - BARCODE
 - UNIQUE SERIAL NUMBER
 - TYCO ELECTRONICS PART NUMBER & ORDER NUMBER
 - ATTENUATION & RETURN LOSS AT 1310 nm

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061321-Y	XY.0

Qty	Description	Item
2	FOAC INFORMATION LABEL	4
1	SC CONNECTOR, SINGLE MODE, BLUE	3
1	LC CONNECTOR, ONE PIECE, SINGLE MODE, BLUE	2
L	FOCAB 2.0S 9/125, YELLOW, LSZH	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 16OCT2009	Tyco Electronics Corporation 's-Hertogenbosch, Nederland	
DIMENSIONS: mm		CHK A. HENGELMOLEN 16OCT2009	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. HENGELMOLEN 16OCT2009	FIBER OPTIC LEAD 2.0S LC/PC - SC/PC SINGLE MODE 9/125	
0 PLC ± -		PRODUCT SPEC	SIZE A2	CAGE CODE 00779
1 PLC ± -		APPLICATION SPEC	DRAWING NO C=2061321	RESTRICTED TO
2 PLC ± -		WEIGHT -	SCALE NTS	SHEET 1 of 1
3 PLC ± -		FINISH -	REV A	
4 PLC ± -				
ANGLES ± -				
MATERIAL -				
		CUSTOMER DRAWING		