




---

 PRODUCT-DETAILS

# OT250KLCC3AZ

## OT250KLCC3AZ Safety switch




---

**General Information**

Extended Product Type	OT250KLCC3AZ
Product ID	1SCA022512R6410
EAN	6417019166131
Catalog Description	OT250KLCC3AZ Safety switch

Long Description	<p>Safety switch, 3-p. 415V AC23 250A, 132kW. Mounted auxiliary contact: 2NO1NC. Steel sheet enclosure. IP65. RedYellow Pistol handle. Interlocked cover. Defeatable interlocking. The enclosed switch is using a galvanised steel enclosure, with polyester coating. It is suitable for outdoor use with respect to UV light and ingress protection. The enclosure have inbuilt gas pressure relief function to protect the user in case of an internal arc. The door is earthed via the hinges. The enclosure is prepared for single and parallel cables. Cable entry types can be blank , ring-flange or C-flange type (FL21), with different cable configuration, like top/bottom or bottom/bottom. The handle is padlockable for 3 padlocks, cover is interlocked, and interlock function can be bypassed for thermographing.</p>
------------------	--

---

**Material Compliance**

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
---	-----------------

REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

## Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340016M0005
Mechanical Drawings	OTKM604023P2C.stp

## Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

## Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363090
Country or Territory of Origin	Finland

## Dimensions

Product Net Width	400 mm
Product Net Height	600 mm
Product Net Depth / Length	230 mm
Product Net Weight	19.41 kg

## Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	415 mm
Package Level 1 Depth / Length	710 mm
Package Level 1 Height	325 mm
Package Level 1 Gross Weight	21.1 kg
Package Level 1 EAN	6417019166131

## Technical

Cable Entry Position	Top/Bottom
Cable Outlets Per Side	2xC-flange / 2xC-flange, Knock-outs: 10mm, 12.5mm, 20.5mm, 25.5mm, 32.5mm
Color	RAL7032
Connecting Capacity Main Circuit	Hole Diameter 8 mm Screw Clamp / PE Terminal 4pc,10 ... 70+4pc M8 mm <sup>2</sup>

Conventional Thermal Current ( $I_{the}$ )	Fully Enclosed 250 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Steel sheet
Handle Color	Red / Yellow
Handle Type	Pistol handle
Impact Resistance Rating	Housing IK09
Maximum Mounted Auxiliary Contacts	2 NO, 2 NC
Mounted Auxiliary Contacts	2 NO, 1 NC
Neutral Type	No Neutral Terminal
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	2
Number of Poles	3P
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 6.5 W
Rated Conditional Short-Circuit Current ( $I_{nc}$ )	40.5 kA
Rated Insulation Voltage ( $U_i$ )	750 V
Rated Operational Current AC-22A ( $I_e$ )	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Current AC-23A ( $I_e$ )	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Power AC-23A ( $P_e$ )	(380 ... 415 V) 132 kW (500 V) 160 kW (690 V) 200 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity ( $I_{cm}$ )	(1000 V AC) 30 kA
Rated Short-time Withstand Current Low Voltage ( $I_{cw}$ )	for 1 s 8 kA
Recommended Screw Driver	Main Circuit M8
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 22 N·m

---

### Technical UL/CSA

Recommended Screw Driver	Main Circuit M8
Tightening Torque	Main Circuit 22 N·m

---

### Certificates and Declarations

Declaration of Conformity - CE	1SCC340025D2704
--------------------------------	-----------------

---

## External Classifications and Standards

---

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

---

---

## Categories

---

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

