




Terminals & Splices > Splices



Wire Size: 1.25 – 2 mm²

Sealable: No

Splice Features: Standard

Barrel Inside Diameter: 2.16 mm [.085 in]

Features

Product Type Features

Splice Accessory Type	Splice
Sealable	No
Splice Type	Butt Splice
Serrated	Yes
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Serrations	16
Compatible With Wire & Cable Type	Discrete Wire

Body Features

Weight per Piece	1.089 g
Plating Material	Tin
Splice Features	Standard
Primary Product Material	Copper



Contact Features

Barrel Type	Closed
-------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Outside Diameter	4.19 mm[.165 in]
Wire Size	2050 – 5180 CMA
Barrel Inside Diameter	2.16 mm[.085 in]
Terminal Material Thickness	.84 mm[.033 in]
Overall Product Length	14.4 mm[.567 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
Compatible With Wire Base Material	Copper

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Other

Military Category	No
-------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223)




	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 58545-1 SOLISTRAND 10-22 DIE ASSY	 TE Part # 49935 DAHT SOLIS 22-10 ASSY	 TE Part # 58546-1 PC 22-10 SOLISSPICE SPL I SHT	 TE Part # 58545-3 SDE DIE ASSY. 22-10 SOLISTRAND
 TE Part # 47813 DIES SOLIS 16-14 DIE SET	 TE Part # 539662-2 MATR SOLISTR 0,3-6,	 TE Part # 169400 CERTI-LOK	 TE Part # 58545-4 SOLISTRAND 10-22 DIE ASSY.

Customers Also Bought



TE Part #1-66358-6
III+ SKT,18-14,TIN ,STRIP



TE Part #967279-001
CES-2



TE Part #2056350007
ES-CAP-NO.3-B8-0-50MM




TE Part #DTP06-4S
PLG, 4P, GRY, N




TE Part #WM-4P
WEDGE LOCK, 4P, REC, ORG, DTM



TE Part #0460-204-12141
PIN, SOLID, SIZE 12, 12-14AWG, NI



TE Part #848633-001
CES-4



TE Part #58425-2
DIE,COAX 128/178X042 SQ IS9657



TE Part #1423176-6
EGPD004=RLY,NUC,GEN. PURP,125



TE Part #1-1437436-6
CR0111=34123-00-RETAINING SPRING KIT

Documents

Product Drawings

SPLICE,SOLIS BUTT 16-14

English

CAD Files

Customer View Model

ENG_CVM_CVM_8-31819-1_U.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-31819-1_U.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-31819-1_U.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SOLISTRAND - QRG

English

RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES

English