

Features

- Tough, flexible and durable even under very cold working conditions.
- Constructed for higher vacuums and pressures.
- Minimum frictional loss is achieved by the smooth bore.
- RoHS 3 compliant.
- Constructions
Manufactured with a white rigid crush and kink resistant anti shock PVC spiral helix encapsulated in the industry standard blue flexible oil resistant PVC cover, with a smooth inside wall.

RS PRO Hose Pipes & Flex Tubes

RS Stock No.: 0336796



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Oil-resistant hose, ideal for any kind of heavy-duty application that involves the transportation of fuels and oils. When it comes to any chemical, it's important to choose a hose suitable for this type of working environment. Our Oil Resistant Delivery Hose is specially developed for oil and fuel transport applications. A medium-weight delivery hose, specially developed for the suction and delivery of diesel, petrol and mineral-based oils/fuels. Reinforced with a rigid crush and kink-resistant white PVC helix. This hose is tough but still extremely flexible, with optimum flow maintained by the smooth bore.

Key Features

Resistant to a wide range of fuels and oils.

- Tough, flexible and durable even under very cold working conditions.
- Constructed for higher vacuums and pressures.
- Minimum frictional loss is achieved by the smooth bore.
- RoHS 3 compliant.

Construction

Manufactured with a white rigid crush and kink resistant anti shock PVC spiral helix encapsulated in the industry standard blue flexible oil resistant PVC cover, with a smooth inside wall.

Application: Transportation – fuels and oils

General Specifications

Hose Pipe / Flexible Tube	Flexible Tube
Colour	Blue
Features	Flexible
Series	RS PRO MDOR
Inner Diameter	25.4mm
Outer Diameter	33.8mm
Material	PVC
Hose Pipe Action	Transfer, Vacuum
Maximum Working Pressure	9.3bar
Suitable Application	Fuel & Oil
Minimum Operating Temperature	-10°C
Maximum Operating Temperature	+55°C
Length	30m
Reinforced	Yes
Bend Radius	113mm
Standards Met	RoHS 3