

MERKMALE

- Kann anstelle eines Sechskantbolzens verwendet werden, wenn es vorhanden ist Weniger Spiel
- Die Kopfhöhe entspricht dem Schaftdurchmesser
- Innensechskantschraube - stärkste aller Kopfausführungen
- Verschiedene Gewindegrößen erhältlich

RS Pro M4 x 12 mm Innensechskant- Sechskantschraube, einfach Edelstahl

RS Best.-Nr. 281-035



Professionelle Produkte von RS bieten Ihnen hochwertige Teile in allen Produktkategorien. Unsere Produktpalette wurde von Ingenieuren getestet und bietet eine vergleichbare Qualität wie die führenden Marken, ohne einen Premium-Preis zu zahlen.

Produktbeschreibung

Die Senkkopf-Innensechskantschrauben von RS PRO sind eine ausgezeichnete Wahl, wenn Sie ein Befestigungselement suchen, das bündig oder unter der Oberfläche Ihres Materials sitzt. Diese beliebten Senkkopfschrauben mit metrischem Gewinde bestehen aus Edelstahl A2 (304) und wurden für leichte Aufgaben mit begrenztem Platzbedarf entwickelt. Diese Befestigungselemente werden dort eingesetzt, wo eine starke, zuverlässige Verbindung erforderlich ist. Diese Schrauben haben eine attraktive, hochwertige Erscheinung und Oberfläche, wo auch immer sie verwendet werden, und bieten außergewöhnliche Beständigkeit gegen Korrosion.

Allgemeine

Gewindegröße	M4
Kopfform	Sechskant-Steckschlüsselkappe
Material	Edelstahl
Oberfläche	Einfach
Gewindetyp	Metrisch
Anwendungen	Holzbearbeitung, Haushaltsanwendungen, Befestigungselemente und Befestigungen, Werkzeugmaschinen und Reparatur, Sicherheitsschutz, Tafelbau

Mechanische

Länge	12mm
Edelstahlausführung	304 A2
Gewindesteigung	0.7mm
Kopfdurchmesserbereich	6,78 mm bis 7,22 mm
Kopfhöhenbereich	3,82 mm bis 4 mm
Nennbereich der Schlüsselgröße	3,02 mm bis 3,08 mm
Schlüsseleinbindung	2mm

Zulassungen

Konformität/Zertifizierung

RoHS-Konformitätszertifikat, DIN912, ISO4762, ANSI B18



Please view our full range listing below for all A2 304 Stainless Steel Hexagon Cap Socket Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Stainless Steel	M3	6 mm	280981
Hex Socket Cap	Stainless Steel	M3	8 mm	280997
Hex Socket Cap	Stainless Steel	M3	10 mm	7976266
Hex Socket Cap	Stainless Steel	M3	12 mm	281007
Hex Socket Cap	Stainless Steel	M3	16 mm	281013
Hex Socket Cap	Stainless Steel	M3	20 mm	293319
Hex Socket Cap	Stainless Steel	M3	25 mm	293325
Hex Socket Cap	Stainless Steel	M3	30 mm	293331

Hex Socket Cap	Stainless Steel	M4	8 mm	281029
Hex Socket Cap	Stainless Steel	M4	10 mm	7976260
Hex Socket Cap	Stainless Steel	M4	12 mm	281035
Hex Socket Cap	Stainless Steel	M4	16 mm	281041
Hex Socket Cap	Stainless Steel	M4	20 mm	290102
Hex Socket Cap	Stainless Steel	M4	25 mm	281057
Hex Socket Cap	Stainless Steel	M4	30 mm	290118
Hex Socket Cap	Stainless Steel	M4	40 mm	293347
Hex Socket Cap	Stainless Steel	M5	10 mm	281063
Hex Socket Cap	Stainless Steel	M5	12 mm	281079
Hex Socket Cap	Stainless Steel	M5	16 mm	281085
Hex Socket Cap	Stainless Steel	M5	20 mm	281091
Hex Socket Cap	Stainless Steel	M5	25 mm	290124
Hex Socket Cap	Stainless Steel	M5	30 mm	290130
Hex Socket Cap	Stainless Steel	M5	40 mm	293353
Hex Socket Cap	Stainless Steel	M5	50 mm	293369

Please view our full range listing below for all A2 304 Stainless Steel Hexagon Cap Socket Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Stainless Steel	M6	10mm	7976279
Hex Socket Cap	Stainless Steel	M6	12 mm	281108
Hex Socket Cap	Stainless Steel	M6	16 mm	281114
Hex Socket Cap	Stainless Steel	M6	20 mm	281120
Hex Socket Cap	Stainless Steel	M6	25 mm	281136
Hex Socket Cap	Stainless Steel	M6	30 mm	290146
Hex Socket Cap	Stainless Steel	M6	35 mm	293375
Hex Socket Cap	Stainless Steel	M6	40 mm	293381
Hex Socket Cap	Stainless Steel	M6	45 mm	293397
Hex Socket Cap	Stainless Steel	M6	50 mm	293404
Hex Socket Cap	Stainless Steel	M6	60 mm	293410

Hex Socket Cap	Stainless Steel	M8	16 mm	281142
Hex Socket Cap	Stainless Steel	M8	20 mm	281158
Hex Socket Cap	Stainless Steel	M8	25 mm	281164
Hex Socket Cap	Stainless Steel	M8	30 mm	281170
Hex Socket Cap	Stainless Steel	M8	35 mm	293426
Hex Socket Cap	Stainless Steel	M8	40 mm	290152
Hex Socket Cap	Stainless Steel	M8	45 mm	7976272
Hex Socket Cap	Stainless Steel	M8	50 mm	293432
Hex Socket Cap	Stainless Steel	M8	60 mm	293448
Hex Socket Cap	Stainless Steel	M10	16 mm	293454
Hex Socket Cap	Stainless Steel	M10	20 mm	293460
Hex Socket Cap	Stainless Steel	M10	25 mm	7976276
Hex Socket Cap	Stainless Steel	M10	30 mm	293476
Hex Socket Cap	Stainless Steel	M10	35 mm	7976285
Hex Socket Cap	Stainless Steel	M10	40 mm	293482
Hex Socket Cap	Stainless Steel	M10	50 mm	293498
Hex Socket Cap	Stainless Steel	M10	60 mm	293505
Hex Socket Cap	Stainless Steel	M10	70 mm	288935

Please view our full range listing below for all A2 304 Stainless Steel Hexagon Cap Socket Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Stainless Steel	M12	20 mm	288941
Hex Socket Cap	Stainless Steel	M12	30 mm	288957
Hex Socket Cap	Stainless Steel	M12	40 mm	288963
Hex Socket Cap	Stainless Steel	M12	50 mm	288979
Hex Socket Cap	Stainless Steel	M12	60 mm	288985
Hex Socket Cap	Stainless Steel	M12	70 mm	288991

SOCKET HEAD CAP SCREWS DIN 912/ ISO 4762 / ANSI B 18.3.1 M



Head Diameter d2 max. allows for Knurled Head

Thread Size d1	(M1,4)		M1,6		M2		M2,5		M2,6		M3		M4	
Thread Pitch	0,3		0,35		0,4		0,45		0,45		0,5		0,7	
Thread Length b	14		15		16		17		NA		18		20	
Head Dia. d2	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	2,46	2,74	2,86	3,14	3,62	3,98	4,32	4,68	4,82	5,18	5,32	5,68	6,78	7,22
ISO 4762 (1997)			2,86	3,14	3,62	3,98	4,32	4,68			5,32	5,68	6,78	7,22
ANSI B 18.3.1 M (1986)			2,87	3,14	3,65	3,98	4,33	4,68			5,32	5,68	6,80	7,22
Head Height k	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	1,26	1,40	1,46	1,60	1,86	2,00	2,36	2,50	2,46	2,60	2,86	3,00	3,82	4,00
ISO 4762 (1997)			1,46	1,60	1,86	2,00	2,36	2,50			2,86	3,00	3,82	4,00
ANSI B 18.3.1 M (1986)			1,52	1,60	1,91	2,00	2,40	2,50			2,89	3,00	3,88	4,00
Key Size nominal s	1,3		1,5		1,5		2		2		2,5		3	
	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	1,32	1,36	1,52	1,56	1,52	1,56	2,02	2,06	2,02	2,06	2,52	2,58	3,02	3,08
ISO 4762 (1997)			1,52	1,56	1,52	1,56	2,02	2,06			2,52	2,58	3,02	3,08
ANSI B 18.3.1 M (1986)			1,520	1,545	1,520	1,545	2,020	2,045			2,52	2,56	3,020	3,071
Key Engagement t	min.		min.		min.		min.		min.		min.		min.	
DIN 912 (1983)	0,6		0,7		1		1,10		1,2		1,3		2	
ISO 4762 (1997)			0,7		1		1,10				1,3		2	
ANSI B 18.3.1 M (1986)			0,8		1		1,25				1,5		2	

Thread Size d1	M5		M6		M8		M10		M12		(M14)		M16	
Thread Pitch	0,8		1		1,25		1,5		1,75		2		2	
Thread Length b	22		24		28		32		36		40		44	
Head Dia. d2	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	8,28	8,72	9,78	10,22	12,73	13,27	15,73	16,27	17,73	18,27	20,67	21,33	23,67	24,33
ISO 4762 (1997)	8,28	8,72	9,78	10,22	12,73	13,27	15,73	16,27	17,73	18,27	20,67	21,33	23,67	24,33
ANSI B 18.3.1 M (1986)	8,27	8,72	9,74	10,22	12,70	13,27	15,67	16,27	17,63	18,27	20,6	21,33	23,58	24,33
Head Height k	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	4,82	5,00	5,7	6,0	7,64	8,00	9,64	10,00	11,57	12,00	13,57	14,00	15,57	16,00
ISO 4762 (1997)	4,82	5,00	5,7	6,0	7,64	8,00	9,64	10,00	11,57	12,00	13,57	14,00	15,57	16,00
ANSI B 18.3.1 M (1986)	4,86	5,00	5,85	6,00	7,83	8,00	9,81	10,00	11,79	12,00	13,77	14,00	15,76	16,00
Key Size nominal s	4		5		6		8		10		12		14	
	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	4,020	4,095	5,02	5,14	6,02	6,14	8,025	8,175	10,025	10,175	12,032	12,212	14,032	14,212
ISO 4762 (1997)	4,020	4,095	5,02	5,14	6,02	6,14	8,025	8,175	10,025	10,175	12,032	12,212	14,032	14,212
ANSI B 18.3.1 M (1986)	4,020	4,084	5,020	5,084	6,020	6,095	8,025	8,115	10,025	10,127	12,032	12,146	14,032	14,159
Key Engagement t	min.		min.		min.		min.		min.		min.		min.	
DIN 912 (1983)	2,5		3		4		5		6		7		8	
ISO 4762 (1997)	2,5		3		4		5		6		7		8	
ANSI B 18.3.1 M (1986)	2,5		3		4		5		6		7		8	

Thread Size d1	(M18)		M20		(M22)		M24		(M27)		M30		M33	
Thread Pitch	2,5		2,5		2,5		3		3		3,5		3,5	
Thread Length b	48		52		56		60		66		72		78	
Head Dia. d2	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	26,67	27,33	29,67	30,33	32,61	33,39	35,61	36,39	39,61	40,39	44,61	45,39	49,61	50,39
ISO 4762 (1997)			29,67	30,33			35,61	36,39			44,61	45,39		
ANSI B 18.3.1 M (1986)			29,53	30,33			35,48	36,39			44,42	45,39		
Head Height k	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	17,57	18,00	19,48	20,00	21,48	22,00	23,48	24,00	26,48	27,00	29,48	30,00	32,38	33,00
ISO 4762 (1997)			19,48	20,00			23,48	24,00			29,48	30,00		
ANSI B 18.3.1 M (1986)			19,73	20,00			23,70	24,00			29,67	30,00		
Key Size nominal s	14		17		17		19		19		22		24	
	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	14,032	14,212	17,05	17,23	17,05	17,23	19,065	19,275	19,065	19,275	22,065	22,275	24,065	24,275
ISO 4762 (1997)			17,05	17,23			19,065	19,275			22,065	22,275		
ANSI B 18.3.1 M (1986)			17,050	17,216			19,065	19,243			22,065	22,319		
Key Engagement t	min.		min.		min.		min.		min.		min.		min.	
DIN 912 (1983)	9		10		11		12		13,5		15,5		18	
ISO 4762 (1997)			10				12				15,5			
ANSI B 18.3.1 M (1986)			10				12				15,0			

