



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Black**

Primary Product Material: **Nylon**

Number of Positions: **36**

Operating Temperature (Max): **85 °C [185 °F]**

Features

Product Type Features

Sealable	No
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	36
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With
---------------	------

Usage Conditions

Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Packaging Features

Packaging Method	Bag
------------------	-----



Packaging Quantity

100

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 2-380937-0
MR SPLT GROMET .312 DIA BLK LF



TE Part # 2-380936-0
MR SPLT GROMET .375 DIA BLK LF



TE Part # 2-380935-0
MR SPLT GROMET .437 DIA BLK LF


Also in the Series | AMP Miniature Rectangular MR



Connector Caps & Covers(15)




Connector Contacts(20)



Connector Hardware(2)



Connector Strain Relief(9)




PCB Headers & Receptacles(57)



Power Contacts(20)



Rectangular Power Connectors(77)



Wire-to-Board Headers & Receptacles (57)

Customers Also Bought




TE Part #7-1393254-7
W92-X112-30=M6/M7/M9/W6/W7



TE Part #1-5747871-3
09 PLUG SP/FMS SCRLK




TE Part #5-104078-4
30 SYSTEM 50 RCPT ASSY DRST SN




TE Part #640506-3
36P MR HDR ASSY V0




TE Part #54010-1
CPC STRAIN RELIEF,SIZE 11



TE Part #640499-3
04P MR HDR ASSY V0



TE Part #641300-1
MR RECPT PTPHBZ LP 26-18



TE Part #1445730-1
STRN RELIEF ASY,STRT SIZE 8



TE Part #7-1393114-3
KUHP-11DT1-24=KU



TE Part #1445390-3
PLUG,8-4,LG INS,STD KEY

Documents



Product Drawings

36P STR/REL HSG HNGD V0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_480594-1_AG.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_480594-1_AG.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_480594-1_AG.3d_stp.zip

English

Customer View Model

ENG_CVM_480594-1_P.3d_igs.zip

English

Customer View Model

ENG_CVM_480594-1_P.3d_stp.zip

English

Customer View Model

ENG_CVM_480594-1_P.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP* MINIATURE RECTANGULAR II (MRII) CONNECTORS

English