

A2101 A2102 A2102/Laser A2103 A2103/LSR Laser

Page 1	
Operating instructions for	
Advent Hand Tachometer mode	els
Page 7	
Mode d'emploi Tachymètres	
Optiques Numériques Série	
Advent, Modèles	
Seite 14	
Bedienungsanleitung Digitale	s
optisches Drehzahlmesser	
Advent-Serie Modell	
Pagina 20	_
Istruzioni per l'uso Tachimetro	0
ottico digitale Modelli Serie	
Advent	
Página 27	
Instrucciones de Operación	
Tacómetro Optico Digital Serio	е
Advent Modelos	

Operating instructions for Advent Hand Tachometer models A2101, A2012, A2102/LSR Laser A2103, A2103/LSR Laser

General features of models

All models feature a patented **vertical LCD display** that gives very good viewability in most applications, with the exception of the A2101 model, all have an "**Inverting display feature**" which maintains the display in the correct plain for the user, for example when pointing the unit down into machinery.

The **A2101** basic model, provides simplicity of operation, has uncomplicated single measurement range and operates at distances up to 0.5m from a reflective target using a highly reliable Minilamp optical system, this model does not have the display inverting feature or reading hold.

A2102 versions, both models include the unique display inverting feature for greater flexibility in operation in almost any application where access is difficult within confined areas, the **A2102/LSR** Laser version provides enhanced optical performance, both are supplied with a Contact adaptor for rpm & linear speed contact applications.

Both A2103 models feature comprehensive specifications, including Maximum and Minimum speed Capture and Average speed modes, model A2103 has the standard visible incandescent Minilamp and model A2103/LSR has an enhanced Laser light system for even wider application and greater performance.

Compact Instruments Ltd April 1999 www.compactinstruments.co.uk

Model A2101 Features and Operation

Display features

- LCD Vertical, 5 digit display (without Display type

backlight) - ves

On target indicator Low Battery indicator - ves

- rpm legend Function indication

Controls - Push-button

On/Off normal mode - Single action Rocker type "push to measure"

- Not used (used on other models of Advent Other controls

Tachometer only)

Optical range

- 50mm - 500mm Optical range

- +/- 45 Deg. to reflective marker Optical angle

Light source - Minilamp visible light

Measurement range

RPM range - 60 - 19,999 rpm (single range)

Resolution - +/- 1 rpm Accuracy - 0.01% +/- 1 digit

Memory features - none

Contact adaptor - not functional on this model

Operation and Use of Model A2101

Ensure the machine to be measured is in a safe off mode. 1. 2. Attach small reflective target to machine shaft (6mm x 25mm)

Start machine and point the Tachometer towards the target. 3. Press and hold the On/Off button at the forward arrow position and 4.

hold continuously. Aim light beam onto target, ensure 'on-target' sign is on at bottom of display screen.

Take rom reading.

7. Note that the display will illuminate only while measurement is taking

Release on/off button and display will clear - no memory retention is

available

Models A2102 and A2102/LSR features and operation

Optical systems - Two types of optical system are used: -

Model A2102 has the standard visible light source via an incandescent Minilamo Model A2102/LSR has enhanced optical Laser light system for greater optical performance.

Both models have a fully autoranging measurement system as standard.

Common Display features & Specification - Models A2102 & A2102/LSR

Display - Inverting LCD Vertical 5 digit display

Display functions - 180 deg. Inverting

On target indicator - Yes Low Battery indicator - Yes

Function icons - "rpm" & "mt" for metres/minute

Controls - 3 push-buttons

Program control

On/off normal mode - Dual action rocker type touch push-button (UP ARROW)

On/off inverted mode - As above but for inverted operation (DOWN

ARROW)

- Selects rpm or metres/minute modes (mt

symbol) Optical system - model A2102

Optical range

- 50mm - 1000mm

Optical angle - +/- 45 Deg. to reflective marker

Light source - Minilamp visible light

Optical system - Laser model A2012/LSR

Optical range

Angle of operation

- 50mm - 2000mm

- +/- 80 Deg. to reflective marker

Light source

- Red Spot Laser Class II (670nm)

Measurement range - both models

Measurement ranges

- rpm (optical) & rpm or metres/min with contact adaptor supplied.

Autoranging function

Autoranging only

Speed range rpm

- 3 - 99,999 rpm

Linear Metres/min

- 0.30 - 1999.9 metres/min

Resolution maximum

- 0.01 in slowest speed range

Accuracy Timebase

- 0.8 seconds or time between pulses,

- 0.01% +/- 1 digit whichever is longest

Operation and Use of Models A2102 & A2102/LSR

Optical rpm measurement

Ensure the machine to be measured is in a safe off mode.

Attach small reflective target to machine shaft (typically 6mm x 25mm. 2. less for laser).

Start machine and point the Tachometer at the target. 3. 4.

Press and hold continuously either of the On/Off buttons to suit application.

5. Aim light beam onto target, ensure "on-target" sign is glowing or flashing steadily.

6. Read rpm, releasing button will hold last reading in the display for 1 minute

Press either On button to zero reading or take another measurement.

Contact rpm measurement

- Fit contact adaptor into the Tachometer and ensure a good click fit 1.
- Start machine and make clean contact with the shaft end. 2.
- Ensure a steady firm pressure is applied to the wheel, just sufficient 3. to maintain slip free contact, excess pressure will wear the rubber tip and bearings and may slow the machine down and give inaccurate readings.
- Releasing the On/Off switch will hold the reading automatically for 1 4. minute.

Linear contact speed measurement - Metres/minute

- Fit contact adaptor as above.
- 2. Press and hold the On button, then press the program button, the display will alternate between the "rpm and mt" symbols, release the program button when the "mt" symbol is illuminated, the instrument is now in the metric linear speed.
- Keeping the On button pressed, now place the contact wheel on the 3. moving surface and read th linear rate.
- Releasing the On button will then hold the last reading in the display for 1 minute.
- 5. The instrument retains Metres/min ode for continued linear measurments for up to 1 minute from previous reading, by pressing either "Measure" buttons this mode will be held for a further minute.
- 6. The instrument will automatically revert to rpm mode after auto switch off.

Note: Inverted operation

The instrument can be used through 180 deg. rotation (e.g. with the light beam or contact probe pointing downward into a machine), the display inverts so display reading is clear.

Models A2103 & A2103/LSR features and operation

Common Display features & Specification

Display

- Inverting LCD Vertical 5 digit display

- 180 deg. Inverting

Display functions On target indicator - Yes Low Battery indicator

- Yes

-	In	~t	10	0 1	~	ns

- Comprehensive selection of ranges shown in display

Controls - 3 push-buttons

On/off normal mode
On/off inverted mode

- Dual action rocker type touch push-button

(UP ARROW)

Program control - Sele

- As above but for inverted operation (DOWN

ARROW)

- Selects program mode in conjunction with Up/Down switches

Optical system Model A2103

Optical range - 50mm - 1000mm

Optical range

- +/- 45 Deg. to reflective marker

Light source - Minilamp visible light

Optical system - Laser model A2103/LSR

Optical range - 50mm - 2000mm

Angle of operation Light source - +/- 80 Deg.

- Red Spot Laser Class II

Measurement range - both models

Measurement modes

- rpm & rps optically (also Count & Time)
- rpm & rps, metres, yards, feet, per min & per

sec, via contact adaptor
- Count total revs. metres, feet, vards

- Measure Time interval in seconds between

pulses (reciprocal rate)

- Speed Capture feature - Maximum, Minimum or Average rate

Speed range - Optical mode

Contact mode

- 3 - 99,999 rpm (or equivalent in rps)

- Max. 50,000 rpm for 10 sec (or equivalent in rps)

Linear speeds - maximum

- 0.30 - 1500.0 Metres or Yds/min. (4,500 ft/min) or equilavent in seconds
- Fully Autoranging up to 0.001digit or +/- 1

Resolution range features - Fully Autoranging up to 0.0 digit fixed, User selectable

Accuracy speed modes only - 0.01% +/- 1 digit

Count mode resolution

Time interval mode

- +/- 0.1 Metres (or equilavent in all ranges)

- 0 - 99999 seconds Autoranging only (max 0.01 resolution)

Timebase standard

- 0.8 seconds or time between pulses,

whichever is longest

Timebase, Fast modes

- 0.1 seconds auto-selection in Maximum or

Minimum capture mode

Memory features

Contact adaptor

- Last reading held for 1 minute, Auto

Switch Off

- Program settings retained in memory

after power down off

 Included complete with rpm cone & metric wheel assembly (removable)

Power requirements AAA alkaline cells

Standard package

Set of batteries, contact adaptor, pack of renective tape, certificate of calibration, custom carrycase & instructions.

Ex works setting - rpm mode, non autoranging

1. Programming - measurement mode selection

All measurement modes are chosen by this method and once confirmed, selected mode remains in permanent memory until re-programmed by the user.

1.1. To change mode hold programme button on and press up measure button and then release both buttons, the display will now illuminate all icons, and the current range will flash.

- To select new measurement mode press either up or down button to 1.2. scan through the modes, when the required mode icons flash release measure button & press programme button once to confirm settings. for non-speed modes the unit is now programmed and read for use.
- To select mx, mn, av. modes continue to scan through each one, if 1.3. the mode is not required, stop scan when all three icons illuminate continuously, then press programme button once. The instrument is now ready to use. Set parameters will be retained until reprogrammed.

2. Optical revolutions speed measurement - rpm or rps

See section 1.

- Ensure batteries are correctly fitted. 21 2.2.
 - Attach small reflective target to machine shaft (typically 6mm x 25mm, less for laser version)
- Start machine and point the tachometer towards the target. 2.3.
- Press and hold either of the on/off buttons to suit application and hold 2.4. continuously.
- Aim light beam onto target, ensure "on-target" sign is glowing or 2.5. flashing steadily
- Read off rpm, releasing button will hold last reading. 2.6.
- Last rpm reading will be held in display for 1 minute. 2.7.
- Press the On button to zero reading or take another measurement. 2.8.

3. Contact revolution speed measurement - rpm or rps.

- See section 1. Fit contact adaptor into the tachometer and ensure a good click fit 3.1. connection.
- Start machine and make clean contact with the recess in shaft end 3.2. (wheel can be removed).
- Contact the shaft end via the rubber cone, ensure a steady firm 3.3. pressure is applied and that the instrument is in line accurately with
- the machine shaft. Press and hold either up or down measure button as required & read 3.4. speed
- Releasing the On switch will hold the reading automatically for 1 3.5 minute, automatic switch off.

4. Linear contact speeds measurement - metres, yds, feet etc. See section 1.

- Fit contact adaptor as above. 4.1.
- Keeping the on button pressed, now place the contact wheel on the 4.2. moving surface and read the linear rate, ensure wheel is vertical to the moving surface.
- Releasing the on button will then hold the last reading in the display 4.3. for 1 min
- The instrument retains selected measurement mode for further linear 4.4. measurements after switch off until programmed to a different mode.

5. Autorange selection - speed modes only

While taking a measurement using either up or down measure button, 5.1. the user can toggle between auto and non-auto mode by pressing the programme button, in the auto mode, the a icon will illuminate.

6. Average speed monitoring mode - 'av' icon.

See section 1.

- Average speed mode this mode provides a rolling average of the 6.1. last 8 measured values.
- Press and hold the On/off button at the forward arrow position and 62 hold continuously
- Aim light beam onto target, ensure "on-target" sign is on at bottom of 6.3 display screen.
- Take rpm reading. 64
- Note that the display will illuminate only while measurement is taking 6.5
- Release on/off button and display will clear no memory retention is 6.6 available.

Power requirements - 4 x AAA alkaline cells

Standard package

mn.

Includes set of batteries, pack of reflective tape, certificate of conformity & instructions.

7. Operation of Maximum & Minimum modes Speed Capture functions - mx,

See section 1.

- 7.1. Having selected the required mode, i.e. Maximum or Minimum, (mx).
 7.2. You are now ready to Capture a reading "On Demand" but continuing to operate normally.
- 7.3. When a capture test is ready to commence, while the Measure button is held On, press Programme button once, at this point the instrument will switch into high speed Timebase mode, (0.1 Seconds) and will Capture the highest or lowest reading after pressing the Programme button.

button.

Releasing the On button will hold the reading and cancel the Capture mode until another Capture measurement is required, when 7.3. should be repeated.

8. Count measurement mode - cnt

See section 1.

- 8.1. Select mode as described in Measurement mode selection section
- 8.2. For rev Counting optically, point the light beam at the target and the instrument will measure all revs. (pulses) until button is released, the display will hold Count for 1 minute.
- 8.3. By contact method, fit contact adaptor, press speed cone onto the end of the shaft, the Instrument will count revs.

9. Linear Length Totalisation measurements - mt, ft, vd -

See section 1.

- 9.1. Select any linear unit of measurement, press contact wheel onto moving surface and commence Count by pressing & holding Measure button On. Count will increment until button is released.
- 9.2. The displayed value can be scanned through the equivalent values of Metres, Feet, Yards, Count by pressing the Programming button, the instrument automatically calculates the appropriate reading.

Note. Measurement Units will be stored in originally programmed parameter e.g. metres.

10. Time interval measurement - int

See section 1.

- 10.1. Select int mode through Measurement selection mode
- 10.2. This mode allows measurement of Time between pulses from optical system (or contactor).
- 10.3. Optically the instrument will measure the time in seconds between pulses, useful for cycle timing of reciprocating machinery.
- 10.4. (Time in seconds per revolution), which equals reciprocal speed.
- 10.5. Very slow speeds can be measured in this mode below 3 rpm.

11. Display orientation - Inverting function - All modes

- 11.1. The instrument can be used through 180 deg. rotation (e.g. with the light beam pointing downward into a machine), the display inverts so that normal reading can take place.
- 11.2. The UP Button selects normal mode for optical and contact measurements.
- 11.3. The Down button selects the display inversion mode and the whole display including relevant icons will reverse through 180 degrees allowing access to difficult applications.

Temperature specification and storage (LCD Display)
Operating temperature = 0 to + 50 degrees C.
Storage temperature = -10 to + 80 degrees C.

These products are designed and manufactured in the U.K. by Compact Instruments Ltd



Safety Label
Etiquette de securite
Warnaufkleber
Etichetta antinfortunistica
Etiqueta de Seguridad

Laser Models - Caution Note: Avoid looking directly into the Laser light source as temporary dazzling may occur.


Attention - Modèles à Laser Remarque: Eviter de regarder directement dans la source lumineuse du laser, car ceci peut provoquer l'aveuglement temporaire.

Lasermodelle - Achtung Anmerkung: nicht direkt in die Laserlichtquelle blicken, da dieses Licht zur vorübergehender Blendung führen kann.

Modelli laser - Fare attenzione N.B.: Evitare di guardare direttamente la sorgente di luce a laser perché si potrebbe avere un abbagliamento temporaneo.

Precaución - Modelos Láser Nota: Evitar mirar la fuente de luzáser directsmente ya que esto puede causar un desello temporal.

RADIACION LASER RADIATION DO
NOT STARE INTO BEAM CLASS 2
LASER PRODUCT
RAYONNMENT LASER NE PAS
REGARDER FIXEMENT LE FAISCEAU
DU LASER PRODUIT A LASER DE
CLASSE II
LASERSTRAHLUNG NICHT IN DEN
STRAHL BLICKEN LASERPRODUKT
DER KLASSE 2
RADIAZIONE LASER NON GUARDARE
IL FASCIO DI LUCE PRODOTTO
LASER DI CLASSE 2
LASER NO MIRAR EL RAYO
PRODUCTO LASER CLASE 2



Control layout (A2103 shown) for individual features see model details.

Disposition des contrôles (Le tachymètre illustré est Modele A2103) - Se référer aux détails du modèle choisi pour visualiser les caractéristiques individuelles de celui-ci.

Auslegung der Bedienungselemente (A2103). Für diverse Funktionen siehe geräteschreibungen. Disposizione dei comandi (in figura il modello A2103). Per le singole funzioni vedere la descrizione dettagliata del modello. Trazado de controles (se muestra A2103), para caracteristicas individuales véanse los detalles del modelo.