


Product datasheet

Specifications



servo motor BMH - 24 Nm - 4000 rpm - keyed shaft - with brake - IP54

BMH1403P17F2A

⚠ Discontinued on: 9 Feb 2023

EAN Code: 3606485208435

⚠ Discontinued

Main

Device short name	BMH
Product or component type	Servo motor
Maximum mechanical speed	4000 rpm
Continuous stall torque	24 N.m for LXM32.D72N4 at 24 A, 400 V, three phase 24 N.m for LXM32.D72N4 at 24 A, 480 V, three phase
Peak stall torque	71.8 N.m for LXM32.D72N4 at 24 A, 400 V, three phase 71.8 N.m for LXM32.D72N4 at 24 A, 480 V, three phase
Nominal output power	4700 W for LXM32.D72N4 at 24 A, 400 V, three phase 4700 W for LXM32.D72N4 at 24 A, 480 V, three phase
Nominal torque	13.92 N.m for LXM32.D72N4 at 24 A, 400 V, three phase 13.92 N.m for LXM32.D72N4 at 24 A, 480 V, three phase
Nominal speed	3000 rpm for LXM32.D72N4 at 24 A, 400 V, three phase 3000 rpm for LXM32.D72N4 at 24 A, 480 V, three phase
Product compatibility	LXM32.D72N4 at 400...480 V three phase
Shaft end	Keyed
IP degree of protection	IP54 standard
Speed feedback resolution	32768 points/turn x 4096 turns
Holding brake	With
Mounting support	International standard flange
Electrical connection	Rotatable right-angled connectors

Complementary

Range compatibility	Lexium 32
[Us] rated supply voltage	480 V
Network number of phases	Three phase
Continuous stall current	18 A
Continuous power	4.8 W
Maximum current Irms	57.66 A for LXM32.D72N4
Maximum permanent current	62.3 A
Second shaft	Without second shaft end
Shaft diameter	24 mm
Shaft length	50 mm
key width	40 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Feedback type	Multiturn SinCos Hiperface
Holding torque	23 N.m holding brake
Motor flange size	140 mm
Number of motor stacks	3
Torque constant	1.3 N.m/A at 120 °C
Back emf constant	85.9 V/krpm at 120 °C
Number of motor poles	5.0
Rotor inertia	50.27 kg.cm²
Stator resistance	0.22 Ohm at 20 °C
Stator inductance	2.165 mH at 20 °C
Stator electrical time constant	13.6 ms at 20 °C
Maximum radial force Fr	2420 N at 1000 rpm 1920 N at 2000 rpm 1680 N at 3000 rpm
Maximum axial force Fa	0.2 x Fr
Brake pull-in power	19 W
type of cooling	Natural convection
Length	267 mm
Centring collar diameter	130 mm
centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	11 mm
Circle diameter of the mounting holes	165 mm
Net weight	18.5 kg
Sizing reference	BMH1403P
Network number of phases	3
Accuracy error [angular]	4.8 °
Temperature copper hot	135 °C
Temperature magnet hot	100 °C
Temperature magnet rt	20 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26.000 cm
Package 1 Width	20.000 cm
Package 1 Length	60.000 cm
Package 1 Weight	18.530 kg
Unit Type of Package 2	P06
Number of Units in Package 2	6
Package 2 Height	75.000 cm
Package 2 Width	80.000 cm

Package 2 Length	60.000 cm
Package 2 Weight	119.180 kg

Logistical informations

Country of origin	DE
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	5196
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	A7df881f-135f-4256-b8c2-ea55d4c9a151
REACH Regulation	REACH Declaration
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins