




PRODUCT-DETAILS

OS160GD22N1P
OS160GD22N1P SWITCH FUSE



概要信息	
产品型号	OS160GD22N1P
产品ID	1SCA116731R1001
欧洲商品编号(EAN)	6417019488196
目录说明	OS160GD22N1P SWITCH FUSE
详细描述	Switch Fuses,Front Operated,4-pole,22 (Between the Poles),DIN,000,00,Handle and shaft included,Switched - With Solid Link

ABB EcoSolutions	
产品环境声明 - EPD	1SCC311196D0201

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201

RoHS信息	1SCC011020D0201
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	a032e308-e65a-47ff-9afc-87ab85c51f91 Finland (FI)
简化的SCIP	e60714ee-6c6e-41a0-bf82-1f88f05ffd56 Germany (DE)
	6a67bb69-7d2f-41e9-bf9e-3ab62db4e36d France (FR)
	347fc3bf-00f9-4b99-9dbc-514831e4d185 Spain (ES)
	1d1663fa-2206-4568-ae76-e2871a0659b4 Belgium (BE)
	4dbce028-85ed-4cba-97f9-0f5af486af3c Hungary (HU)
	7e199f35-facb-4cd8-8f31-c6b88619a1ad Sweden (SE)
	50aafa-5f87-416b-92d3-1cd8ec72a660 Netherlands (NL)
	520ad1a2-f47f-4542-8bc0-c075364e9dc7 Czech Republic (CZ)
	3bbafb89-25cb-4307-af0e-3f4ebdbcf0a7 Poland (PL)
	2453f52a-4de5-4897-816c-c2f1b1e7c607 France (FR)
	ae3c23bd-0c87-4efd-b889-f3f62bb18b24 Greece (GR)
	64e6f580-3b73-450d-bd8a-ce202a8b302d Bulgaria (BG)
	c6191ddb-e059-4f18-8e60-7a0791f33daf Portugal (PT)
	16bfc11d-4ed6-4840-a4b8-eb2d74db5f0c Sweden (SE)
	4706092d-8674-4c0a-bee0-a89d2aba417b Hungary (HU)
	c993c536-ad76-479f-89e9-3ca471ca3c14 Estonia (EE)
	8625ed95-5e47-4635-8495-05f2e57990da Croatia (HR)
	74ca4b21-46a3-41d0-b342-b1fbe31ab318 Poland (PL)
	12986945-5f7f-4646-8bc0-743a80c0035e Germany (DE)
	1384c776-4b7f-4d1d-86d9-c95767e9c81a Germany (DE)
	07836900-0a77-4e67-970e-fa8f46d72185 Poland (PL)
	fa3f461d-0e01-4dac-baa1-dd58c6770f44 Italy (IT)
	a8566127-b18d-4a3e-9883-5a8b40dc11d0 Belgium (BE)
	435d9e9d-888e-4d44-8868-e76e53f0bad2 Germany (DE)
	42ea9c50-ac07-4046-a345-481298e0f2bd Norway (NO)
	ec34ebd5-3f60-439a-af4c-546ccc9bc7bb Germany (DE)
	4c9b0332-159b-4d26-88e4-5fae52abc38f Denmark (DK)
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

数据手册, 技术资料	1SCC311013C0201
说明书和手册	1SCC311037M0206
机械制图	OS160GD_F_22.igs
产品环境声明 - EPD	1SCC311196D0201

环境条件

污染等级	3
------	---

订货信息

最小起订量	1 piece
海关关税号	85365080
原产地	Finland (FI)

尺寸

产品净宽	183 mm
产品净高	140 mm
产品净深	130 mm
产品净重	2.6 kg
	5.73 lb

包装信息	
1级包装单元	box 1 piece
1级包装宽度	170 mm 6.7 in
1级包装长度	250 mm 9.8 in
1级包装高度	155 mm 6.1 in
1级包装 总重	2.76 kg 6.1 lb
1级包装 EAN	6417019488196

技术参数	
额定发热电流（自由空气）(I _{th})	Θ = 40 °C 160 A
额定发热电流 (I _{the})	Fully Enclosed 160 A
第四个极位	Left Side
第四个极点类型	Switched - With Solid Link
熔断器规格	NH000 NH00
熔断器系列	DIN
手柄类型	Pistol handle and shaft included
安装类型	Base mounting
极数	4P
操作模式	Front Operated
污染等级	3
导线端子位置	Top In - Bottom Out, Bottom In - Top Out
功率损耗	at Rated Operating Conditions per Pole 9 W
额定限制短路电流 (I _{nc})	(690 V) 80 kA
额定电流 (I _n)	Main Circuit 160 A
额定冲击耐受电压 (U _{imp})	8 kV
额定绝缘电压 (U _i)	1000 V
额定工作电流 AC-21A (I _e)	(500 V) 160 A (690 V) 160 A
额定工作电流 AC-22A (I _e)	(500 V) 160 A (690 V) 160 A
额定工作电流 AC-23A (I _e)	(500 V) 160 A (690 V) 160 A
额定工作功率 AC-23A (P _e)	(220 ... 240 V) 45 kW (400 V) 75 kW (415 V) 75 kW (500 V) 90 kW (690 V) 132 kW
额定工作电压	Main Circuit 690 V AC
额定不间断电流 (I _{cw})	for 1 s 5 kiloampere rms
标准	IEC 60947-3
开关操作机构	22 (Between the Poles)
端子类型	Lug terminals
端子宽度	20 mm
拧紧力矩	15 ... 22 N·m

UL/CSA适用的技术参数	
拧紧力矩	15 ... 22 N·m

认证及声明（文件编码）

A2L Certificate – IEC	1SCC311209D0201
ATEX认证	No certification needed
CCC认证	CCC OS100-160G_ 2015.pdf
符合性声明 - CE	1SCC311137D2703
DNV GL Certificate	1SCC311125D0203
UL认证	No certification needed

分类

对象分类代码	Q
ETIM 8	EC001040 - Fuse switch disconnecter
ETIM 9	EC001040 - Fuse switch disconnecter
UNSPSC	39122233
IDEA 粒度分类代码 (IGCC)	5291 >> Fuse switch disconnecter
e级	V11.1 : 27371401
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

分类

低压产品及系统 → 开关类产品 → 开关熔断器组

