



Connection cable, 4p, DC current, coupling M12 flat, plug, angled, L=1.5m

Part no. CSDR4A4CY2201.5-D
136313
EL Number 4315404
(Norway)

General specifications		
Product name		Eaton Moeller® series CSDR Accessory Connection cable
Part no.		CSDR4A4CY2201.5-D
EAN		4015081330959
Product Length/Depth		177.8 millimetre
Product height		25.4 millimetre
Product width		152.4 millimetre
Product weight		0.27 kilogram
Certifications		CE
Product Tradename		CSDR
Product Type		Accessory
Product Sub Type		Connection cable
Product Specification Details		
Ambient operating temperature - max		70 °C
Ambient operating temperature - min		-25 °C
Cable length		1.5 m
Cable sheath material		Other
Cable type		Coupling, straight, Input side Plug, angled, Output side Multi-core
Color cable sheath		Yellow
Contact body material		Other
Contact surface material		Other
Continuity resistor		0 mΩ
Degree of protection		Other
EL number		4315404
Electrical connection type (box-sided)		M12
Electrical connection type (field-sided)		M12
Nominal current		0 A
Number Of Poles		Four-pole
Permitted temperature of outer cable (assembled) without vibration - max		70 °C
Permitted temperature of outer cable (assembled) without vibration - min		40 °C
Permitted temperature of outer cable (assembling/handling) - max		70 °C
Permitted temperature of outer cable (assembling/handling) - min		40 °C
Plug-in contact type (box-sided)		Male (plug)
Plug-in contact type (field-sided)		Female (bus)
Positioning cable feed (box-sided)		Angled
Positioning cable feed (field-sided)		Straight
Product category		Accessories
Rated operational voltage (Ue) - max		0 V
Type		Connecting cables
Voltage type		DC

Technical data ETIM 9.0

Sensors (EG000026) / Sensor-actuator patch cord (EC001855)		
Electric engineering, automation, process control engineering / Cable, wire / Ready-made data cable / Assembled sensor/actuator adapter, with cable (ecI@ss13-27-06-03-13 [AFR625008])		
Number of poles		4
Type of electrical connection, field-sided		M12

Type of plug-in contact, field sided			Female (bus)
Positioning cable feed, field-sided			Straight
Type of electrical connection, box-sided			M12
Type of plug-in contact, box-sided			Male (plug)
Positioning cable feed, box-sided			Angled
Cable length		m	1.5
Material of cable sheath			Other
Halogen free			No
Colour cable sheath			Yellow
With LED indication			No
Screened			No
Cable type			Multi-core
Vulcanize			No
Material contact body			Other
Material of contact surface			Other
Permitted cable outer temperature after assembling without vibration		°C	40 - 70
Permitted cable outer temperature during assembling/handling		°C	40 - 70
Rated current I _n		A	0
Rated voltage		V	0
Continuity resistance		mOhm	0
Degree of protection (IP)			Other