

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight, SPEEDCON, M17, number of positions: 3+PE, contact connection type: Pin, shielded: yes, degree of protection: IP67, cable diameter range: 5 mm ... 9.2 mm, number of positions: 4, connection method: Crimp connection, series: ST, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Reduced size: ideal for compact devices
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly
- Flexible use: reliably connect various cable diameters

Commercial data

Item number	1243228
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRSEF
GTIN	4063151399085
Weight per piece (including packing)	44.6 g
Weight per piece (excluding packing)	44.6 g
Customs tariff number	85366990
Country of origin	DE

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>

Technical data

Notes

Order information:	Order crimp contacts Ø 2 mm separately
Safety note	
Safety note	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property. • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. • The products are suitable for applications in plant, controller, and electrical device engineering. • When operating the connectors in outdoor applications, they must be separately protected against environmental influences. • Assembled products may not be manipulated or improperly opened. • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products). • When using the product in direct connection with third-party manufacturers, the user is responsible. • For operating voltages > 50 V AC, conductive connector housings must be grounded • Ensure that the protective or functional ground has been properly connected. • VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector • Only use tools recommended by Phoenix Contact • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product. • Operate the connector only when it is fully plugged in and interlocked. • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards. • Observe the minimum bending radius of the cable. Lay the cable without twisting it. • The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Circular connector (cable-side)
Series	ST
Application	Power
Number of positions	4
Connection profile	3+PE
Shielded	yes
Coding	N
Thread type	M17

Material specifications

Seal material	FPM
Housing material	Metal

Connection data

Conductor connection

Connection method	Crimp connection
-------------------	------------------

Electrical properties

Contact

Contact diameter	2 mm
Max. current	25 A
Nominal voltage U_N	630 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	6 kV

Contact

Contact diameter	2 mm
------------------	------

Connector

Type	straight
Direction of rotation	Standard

Connection 1

Head design	Pin
-------------	-----

Cable/line

External cable diameter	5 mm ... 9.2 mm
-------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	3000 m

ST-3EP1N8A8K03SX - Cable connector


1243228

<https://www.phoenixcontact.com/in/products/1243228>




Drawings

Schematic diagram



Connector pin assignment

Dimensional drawing




Technical drawings can be found under Downloads

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>



I = current strength, ϑ = ambient temperature, 3x 25 A

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1243228>



cUL Recognized

Approval ID: E335019-20111129



UL Recognized

Approval ID: E335019-20111129



UL Recognized

Approval ID: E153698-20140124



cUL Recognized

Approval ID: E153698-20140124

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>

Classifications

ECLASS

ECLASS-11.0	27440103
ECLASS-12.0	27440103
ECLASS-13.0	27440103

ETIM

ETIM 9.0	EC003570
----------	----------

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

ST-3EP1N8A8K03SX - Cable connector



1243228

<https://www.phoenixcontact.com/in/products/1243228>

Accessories

ST-20KP0,25-2,50 - Crimp contact

1242329

<https://www.phoenixcontact.com/in/products/1242329>



Crimp contact, Pin, turned, contact diameter: 2 mm, crimp range: 0.25 mm² ... 2.5 mm², Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

ST-Z0016 - Color coding

1617993

<https://www.phoenixcontact.com/in/products/1617993>

Color coding, color: green



ST-3EP1N8A8K03SX - Cable connector

1243228

<https://www.phoenixcontact.com/in/products/1243228>




ST-Z0017 - Color coding

1618049

<https://www.phoenixcontact.com/in/products/1618049>

Color coding, color: orange



ST-Z0018 - Color coding

1618050

<https://www.phoenixcontact.com/in/products/1618050>

Color coding, color: black



ST-3EP1N8A8K03SX - Cable connector

1243228

<https://www.phoenixcontact.com/in/products/1243228>



PROT-M17PRO-IT-IP20 - Plastic protective cap

1055709

<https://www.phoenixcontact.com/in/products/1055709>

Plastic protective cap, M17, series: M17 PRO



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in