







STYLE 1



STYLE 2



STYLE 3

PART NO.	"A" DIA.	"B" DIA.	"C" DIA.	"D"	"E"	"F" REF	STYLE NO.
POF-40022	.31 [7.9]	.126 [3.2]	.17 [4.4]	.13 [3.3]	.06 [1.5]	.14 [4.1]	1
POF-40048	.31 [7.9]	.146 [3.7]	.24 [6.1]	.06 [1.6]	.09 [2.3]	.12 [3]	1
POF-40059	.50 [12.7]	.374 [9.5]	.50 [12.7]	.06 [1.6]	.48 [12.2]	.14 [3.6]	2
POF-50185	.53 [13.4]	.236 [6]	.29 [7.3]	.08 [2]	.18 [4.6]	.34 [8.6]	3
POF-12664	.62 [15.7]	.276 [7]	.34 [8.6]	.05 [1.3]	.20 [5.1]	.16 [4.1]	3

NOTES:

1. MATERIAL: THERMOPLASTIC ELASTOMER, UL 94 HB (RMS-262)
2. COLOR: BLACK
3. ALTERNATE UNITS FOR REFERENCE ONLY

3. ALTERNATE UNITS FOR REFERENCE ONLY			TITLE: PUSH ON FEET						
			CREATED USING SOLIDWORKS	FILE #: POF	DWN: SK	APP: R.T.	FINAL		
			TOLERANCES UNLESS NOTED	SHEET: 1 OF 1	SHEET SIZE: A	DT: 11/06/06	CHKD: S.J.	PART #	PRINT TYPE
I	SEE CO #200012 FOR CHANGES	SK 09/14/07	.XX=±.010	RE: RICHCO, INC.		RICHCO, INC.		SEE TABLE	CA
-	SEE ENGINEERING FOR REV A-H	----	.XXX=±.005			ENG@RICHCO-INC.COM			
REV.	DESCRIPTION	ENGR. DATE	FRAC.=±1/64			(773) 539-4060			
			ANG.=±1°						