

FEATURES

- **80W Power Rating:** Provides sufficient power for effective soldering across different components.
- **550°C Soldering Tip Temperature:** Ensures optimal heat for a wide range of soldering tasks.
- **110 – 230 V Input Voltage:** Compatible with various power sources, enhancing versatility.
- **LED Display:** Offers clear visibility of temperature settings for precise control.
- **Type G and Type E Plug Options:** Suitable for use in multiple regions, increasing usability.

RS PRO 80W Soldering Station, 550°C Temperature

RS Stock No: 631-071



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 80W Soldering Station is designed for precision soldering tasks, offering reliable performance for both professional and hobbyist applications. With a maximum temperature of 550°C, it ensures efficient heat transfer for various soldering needs.

General Specifications

Display Type	LED
Number of Outputs	1
Product Type	Soldering Station
Soldering Tip Temperature	550 °C
Tasks Supported	Soldering

Protection Category

ESD Safe	No
----------	----

Electrical Specifications

Input Voltage	110-230 V
Plug Type	Type G - British 3-Pin, Type E - France-2 Round Pin
Power Rating	80 W

Approvals

Standards/Approvals	CE, UKCA
---------------------	----------