

Vacuum Cleaner LXT®

DVC750L

18V • 67 mbar • 7,5 L

**Portable Vacuum cleaner for both wet and dry cleaning.
Powered by 18V LXT Li-Ion battery.**

A cordless vacuum cleaner with a HEPA filter and brushless motor for small-scale worksite cleaning or use with a machine. The vacuum cleaner has two suction power settings and it supports dry functions. 7.5L tank, no dust bag needed.



LXT **BL** **HEPA**
MOTOR filter

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
Air volume	1,6 m³/min
Max. sealed suction	67 mbar
Continuous Use 18V / 5.0 Ah Battery	60 / 30 min
Continuous Use 18V / 6.0 Ah Battery	70 / 35 min
Vacuum hose length	0,5 - 2,0 m
Vacuum hose diameter	28 mm
Tank Capacity for Dust	7,5 L
Tank Capacity for Liquids	4,5 L
Sound Pressure Level (L _{pA})	76 dB(A)
Noise Uncertainty (K Factor)	2,5 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Dust Class	L
Tool weight with battery	4,3 - 4,6 kg

User benefits

- Brushless maintenance-free and long-life motor
- Flexible hose which stretches from 0.5 meter up to 2.0 meters
- Approved for Dust Class L in accordance with the EU standard
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

123486-2

Floor T-Nozzle 225 mm, White



123584-2

Telescopic Pipe Ø 27 x 500 - 850 mm



140G04-3

Vacuum Hose 28 mm x 2 m



162518-0

Hepa Filter complete



191G86-8

Nozzle assembly set



191M39-3

Filter for suction water



417765-1

Adapter 22 mm



418500-0

Joint 28 - 38 mm



424379-9

Front Cuff Ø24mm



Other

User manual

Parts drawing