


# Rotary drive ERMO-25-ST-E

Part number: 3008527

☆ Core product range

FESTO



## Data sheet

Feature	Value
Size	25
Design structure	Electromechanical rotary drive With integrated gearing
Assembly position	Any
Mounting type	with internal (female) thread
Rotation angle	Endless
Gear unit ratio	9:1
Nominal torque	2.5 Nm
Nominal rotary speed	66 1/min
Max. speed	150 1/min
Torsional backlash	0.2 deg
Repetition accuracy	±0,05 °
Max. axial force	350 N
Max. radial force	450 N
Permissible mass moment of inertia	0.0065 kgm <sup>2</sup>
Product weight	1,350 g
Stepper angle at full step	1.8 deg
Stepper angle tolerance	±5%
Mass moment of inertia, JO	0.114 kgcm <sup>2</sup>
Duty cycle	100%
Nominal operating voltage DC	24 V
Nominal motor current	3 A
Insulation protection class	B
Motor type	Stepper motor
Rotor position sensor	Incremental encoder
Rotary position encoder interface	RS422 TTL AB-channel + zero index
Rotary position encoder measuring principle	Optical
Electrical connector system	Plug
Interface code, base	E8-55
Protection class	IP40
Ambient temperature	0 ... 50 °C
Relative air humidity	0 - 85 % non-condensing
Materials note	Contains PWIS substances Conforms to RoHS
CE mark (see declaration of conformity)	to EU directive for EMC
Material flange	Wrought Aluminium alloy Anodised
Material housing	Wrought Aluminium alloy Anodised