



# round cylinder ESNU-40-50-P

Part number: 195875

**FESTO**

As per DIN ISO 6432, with elastic cushioning rings in end positions.  
Various mounting options, with or without additional mounting components.



## Data sheet

Feature	Value
Stroke	50 mm
Piston diameter	40 mm
Piston rod thread	M12x1,25
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Cylinder barrel
Operating pressure	1.2 ... 10 bar
Mode of operation	single-acting pushing action
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 ... 80 °C
Spring return force, retracted	30 N
Theoretical force at 6 bar, return stroke	30 N
Theoretical force at 6 bar, advance stroke	687.6 N
Moving mass	410 g
Moving mass with 0 mm stroke	230 g
Additional weight per 10 mm stroke	24 g
Basic weight for 0 mm stroke	661 g
Product weight	781 g
Additional mass factor per 10 mm of stroke	16 g
Mounting type	with accessories
Pneumatic connection	G1/4
Materials note	Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High alloy steel
Material cylinder barrel	High alloy steel, non-corrosive