


www.vishay.com

Vishay Semiconductors

Thyristor, Surface Mount, Phase Control SCR, 16 A





PRODUCT SUMMARY								
Package	TO-263AB (D ² PAK)							
Diode variation	Single SCR							
I _{T(AV)}	16 A							
V _{DRM} /V _{RRM}	800 V, 1200 V							
V_{TM}	1.25 V							
I _{GT}	45 mA							
TJ	-40 to +125 °C							

FEATURES

- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Designed and qualified according JEDEC®-JESD 47
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912





ROHS COMPLIANT HALOGEN FREE

APPLICATIONS

- Input rectification (soft start)
- Vishay input diodes, switches and output rectifiers which are available in identical package outlines

DESCRIPTION

The VS-25TTS...SPbF High Voltage Series of silicon controlled rectifiers are specifically designed for medium power switching and phase control applications. The glass passivation technology used has reliable operation up to 125 °C junction temperature.

OUTPUT CURRENT IN TYPICAL APPLICATIONS									
APPLICATIONS SINGLE-PHASE BRIDGE THREE-PHASE BRIDGE UNITS									
NEMA FR-4 or G10 glass fabric-based epoxy with 4 oz. (140 μm) copper	3.5	5.5							
Aluminum IMS, R _{thCA} = 15 °C/W	8.5	13.5	A						
Aluminum IMS with heatsink, R _{thCA} = 5 °C/W	16.5	25.0							

Note

T_A = 55 °C, T_J = 125 °C, footprint 300 mm²

PARAMETER	TEST CONDITIONS	VALUES	UNITS
I _{T(AV)}	Sinusoidal waveform	16	•
I _{RMS}		25	А
V _{RRM} /V _{DRM}		800 to 1200	V
I _{TSM}		350	А
V _T	16 A, T _J = 25 °C	1.25	V
dV/dt		500	V/µs
dl/dt		150	A/μs
TJ		-40 to +125	°C

VOLTAGE RATINGS			
PART NUMBER	V _{RRM} , MAXIMUM PEAK REVERSE VOLTAGE V	V _{DRM} , MAXIMUM PEAK DIRECT VOLTAGE V	I _{RRM} /I _{DRM} , AT 125 °C mA
VS-25TTS08SPbF	800	800	10
VS-25TTS12SPbF	1200	1200	10



ABSOLUTE MAXIMUM RATINGS							
PARAMETER	SYMBOL	TEC	T CONDITIONS	VAL	UNITS		
PANAMETEN	STIMBUL	31MBOL TEST CONDITIONS				UNITS	
Maximum average on-state current	I _{T(AV)}	T _C = 93 °C, 180° c	onduction half sine wave	1	6		
Maximum RMS on-state current	I _{RMS}			2	:5	Α	
Maximum peak, one-cycle,		10 ms sine pulse,	rated V _{RRM} applied	3	00		
non-repetitive surge current	I _{TSM}	10 ms sine pulse,	no voltage reapplied	3	50		
Maximum I ² t for fusing	l ² t	10 ms sine pulse,	rated V _{RRM} applied	4:	50	A ² s	
Maximum 1-t for fusing	1-1	10 ms sine pulse, no voltage reapplied		630		A-S	
Maximum I ² √t for fusing	I²√t	t = 0.1 ms to 10 m	t = 0.1 ms to 10 ms, no voltage reapplied			A²√s	
Maximum on-state voltage drop	V_{TM}	16 A, T _J = 25 °C		1.25		V	
On-state slope resistance	r _t	T 105 °C	12.0		2.0	mΩ	
Threshold voltage	V _{T(TO)}	$V_{T(TO)}$ $T_J = 125 ^{\circ}\text{C}$ 1.0		.0	V		
Maximum various and divest leakage arrest	1 /1	T _J = 25 °C	V Dated V A	0	.5		
Maximum reverse and direct leakage current	I _{RM} /I _{DM}	$T_{J} = 125 ^{\circ}\text{C}$ $V_{R} = \text{Rated } V_{RRM}/V_{DR}$		1	0		
Holding current	I _H	VS-25TTS08, VS-25TTS12 Anode supply = 6 V, resistive load, initial $I_T = 1$ A, $I_J = 25$ °C		-	150	mA	
Maximum latching current	ΙL	Anode supply = 6 V, resistive load, T _J = 25 °C			00		
Maximum rate of rise of off-state voltage	dV/dt	$T_J = T_J \text{ max., linear to } 80 \text{ %, } V_{DRM} = R_g - k = Open$			00	V/µs	
Maximum rate of rise of turned-on current	dl/dt		-			A/µs	

TRIGGERING	TRIGGERING							
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS				
Maximum peak gate power	P _{GM}		8.0	W				
Maximum average gate power	P _{G(AV)}		2.0	VV				
Maximum peak positive gate current	+ I _{GM}		1.5	Α				
Maximum peak negative gate voltage	- V _{GM}		10	V				
		Anode supply = 6 V, resistive load, T_J = - 10 °C	60	mA				
Maximum required DC gate current to trigger	I _{GT}	Anode supply = 6 V, resistive load, T_J = 25 °C	45					
		Anode supply = 6 V, resistive load, T _J = 125 °C	20					
		Anode supply = 6 V, resistive load, T_J = - 10 °C	2.5					
Maximum required DC gate voltage to trigger	V_{GT}	Anode supply = 6 V, resistive load, T _J = 25 °C	2.0	V				
		Anode supply = 6 V, resistive load, T _J = 125 °C	1.0	V				
Maximum DC gate voltage not to trigger	V_{GD}	T 105 °C V Detect value	0.25					
Maximum DC gate current not to trigger	I _{GD}	T _J = 125 °C, V _{DRM} = Rated value	2.0	mA				

SWITCHING								
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS				
Typical turn-on time	t _{gt}	T _J = 25 °C	0.9					
Typical reverse recovery time	t _{rr}	T _{.I} = 125 °C	4	μs				
Typical turn-off time	t _q	1J = 125	110					

THERMAL AND MECHANICAL SPECIFICATIONS								
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS				
Maximum junction and storage temperature range	T _J , T _{Stg}		-40 to +125	°C				
Soldering temperature	T _S	For 10 s (1.6 mm from case)	260					
Maximum thermal resistance, junction to case	R _{thJC}	DC operation	1.1	°C/W				
Typical thermal resistance, junction to ambient (PCB mount)	R _{thJA} ⁽¹⁾		40	O/VV				
Approximate weight			2	g				
Approximate weight			0.07	OZ.				
Marking daving		Case style D ² PAK (SMD-220)	25TTS08S					
Marking device		Case style D-FAN (SIVID-220)	25TTS12S					

Note

⁽¹⁾ When mounted on 1" square (650 mm²) PCB of FR-4 or G-10 material 4 oz. (140 µm] copper 40 °C/W For recommended footprint and soldering techniques refer to application note #AN-994




Fig. 1 - Current Rating Characteristics




Fig. 2 - Current Rating Characteristics





Fig. 3 - On-State Power Loss Characteristics



Average On-state Current (A)
Fig. 4 - On-State Power Loss Characteristics

www.vishay.com

Vishay Semiconductors




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current





Fig. 7 - On-State Voltage Drop Characteristics







Fig. 9 - Thermal Impedance Z_{thJC} Characteristics

ORDERING INFORMATION TABLE

Device		~~
Devic	æc	oue



- Vishay Semiconductors product
- Current rating (25 = 25 A)
- Circuit configuration:
 - T = single thyristor
- Package:
- T = TO-220AC 5 Type of silicon:
- S = standard recovery rectifier 08 = 800 V6 Voltage rating: voltage code x 100 = V_{RRM} 12 = 1200 V
- 7 S = TO-220 D²PAK (SMD-220) version
- None = tube
 - TRL = tape and reel (left oriented)
 - TRR = tape and reel (right oriented)
- 9 PbF = lead (Pb)-free

ORDERING INFORMATION (Example)									
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION						
VS-25TTS08SPbF	50	1000	Antistatic plastic tubes						
VS-25TTS08STRRPbF	800	800	13" diameter reel						
VS-25TTS08STRLPbF	800	800	13" diameter reel						
VS-25TTS12SPbF	50	1000	Antistatic plastic tubes						
VS-25TTS12STRRPbF	800	800	13" diameter reel						
VS-25TTS12STRLPbF	800	800	13" diameter reel						

LINKS TO RELATED DOCUMENTS						
Dimensions <u>www.vishay.com/doc?95046</u>						
Part marking information	www.vishay.com/doc?95054					
Packaging information	www.vishay.com/doc?95032					



D²PAK

DIMENSIONS in millimeters and inches



SYMBOL	MILLIM	ETERS	INC	HES	NOTES	NOTES		MILLIM	ETERS	INC	HES	NOTES
STIVIBUL	MIN.	MAX.	MIN.	MAX.	NOIES		SYMBOL	MIN.	MAX.	MIN.	MAX.	NOTES
Α	4.06	4.83	0.160	0.190			D1	6.86	8.00	0.270	0.315	3
A1	0.00	0.254	0.000	0.010			Е	9.65	10.67	0.380	0.420	2, 3
b	0.51	0.99	0.020	0.039			E1	7.90	8.80	0.311	0.346	3
b1	0.51	0.89	0.020	0.035	4		е	2.54	BSC	0.100) BSC	
b2	1.14	1.78	0.045	0.070			Н	14.61	15.88	0.575	0.625	
b3	1.14	1.73	0.045	0.068	4		L	1.78	2.79	0.070	0.110	
С	0.38	0.74	0.015	0.029			L1	-	1.65	-	0.066	3
c1	0.38	0.58	0.015	0.023	4		L2	1.27	1.78	0.050	0.070	
c2	1.14	1.65	0.045	0.065			L3	0.25	BSC	0.010	BSC	
D	8.51	9.65	0.335	0.380	2		L4	4.78	5.28	0.188	0.208	

Notes

- (1) Dimensioning and tolerancing per ASME Y14.5 M-1994
- (2) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outmost extremes of the plastic body
- (3) Thermal pad contour optional within dimension E, L1, D1 and E1
- (4) Dimension b1 and c1 apply to base metal only
- (5) Datum A and B to be determined at datum plane H
- (6) Controlling dimension: inch
- (7) Outline conforms to JEDEC® outline TO-263AB



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000