




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Natural**

Primary Product Material: **Polyester**

Number of Positions: **17**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	17
---------------------	----

Body Features

Primary Product Color	Natural
Primary Product Material	Polyester

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
Operating Temperature (Max)	105 °C[221 °F]



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-640387-7
17P MTA156 HDR ASSY SQ R/A



TE Part # 1-640388-7
17P MTA156 HDR ASSY RN STR F/L



TE Part # 1-644753-7
17P MTA156 HDR ASSY RN STR F/L



TE Part # 1-1744194-7
17P MTA156 HDR ASSY FL/STR SN



TE Part # 4-640428-7
17P MTA156 CONN ASSY 22AWG RED

TE Part # 4-641208-7
17P MTA156 HDR ASSY FL ST LF

TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board,
with Mating Alignment, SL156

TE Part # 644959-1
17P MTA156 R/A ASY WO4,8,12,15

TE Part # 644873-2
17P MTA156 HDR ASSY W/O#11

TE Part # 4-641120-7
17P MTA156 HDR ASSY FL/ST LF

TE Part # 4-641207-7
17P MTA156 HDR ASSY FL RA LF

TE Part # 641623-1
MTA156 KEYING PLUG (10/STRIP)

TE Part # 4-641119-7
17P MTA156 HDR ASSY FL/ST LF

TE Part # 1-644752-7
17P MTA156 HDR ASSY SQ STR F/L

TE Part # 1-640251-7
17P SL156 HSG W/O LCK RAMP

TE Part # 1-640389-7
17P MTA156 HDR ASSY SQ R/A F/L

TE Part # 4-643817-7
17P MTA156 CONN ASSY 18AWG LF

TE Part # 4-643819-7
17P MTA156 CONN ASSY 22AWG LF

TE Part # 4-640602-7
17P MTA156 CONN ASSY 24AWG LF

TE Part # 4-640605-7
17P MTA156 CONN ASSY 20AWG LF

Also in the Series | MTA 156

Connector Caps & Covers(89)

Connector Contacts(4)

Connector Hardware(2)


PCB Headers & Receptacles(677)



Power Contacts(3)




Rectangular Power Connectors(1178)



Standard Rectangular Connectors(667)


Customers Also Bought



TE Part #233829-000
202A132-25/225-0




TE Part #1577631-1
TERMINAL RT PIDG PEEK STRATO 18-16 AWG



TE Part #206358-5
CABLE CLAMP ASY, SIZE 11




TE Part #650139-000
D-436-52




TE Part #36906
SPLICE,SOLIS BUTT 8



TE Part #620143-000
D-101-31



TE Part #ER6593-000
D-436-37CS9376



TE Part #679953-000
B-013-10CS2689

Documents

Product Drawings
17P MTA156 COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-640551-7_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-640551-7_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-640551-7_G.3d_stp.zip

English

Customer View Model



[ENG_CVM_1-640551-7_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-640551-7_L.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-640551-7_L.2d_dxf.zip](#)

English

[3D PDF](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

Japanese

[Application Specification](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese