




Terminals & Splices > Foil Terminals



Accepts Foil Thickness (Max): .8 mm [.031 in]

Terminal Plating Material: Tin

Packaging Method: Reel

Features

Contact Features

Terminal Plating Material	Tin
---------------------------	-----

Termination Features

Accepts Foil Thickness (Max)	.8 mm[.031 in]
------------------------------	----------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)




Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | **TERMI-FOIL**



Foil Terminals(23)

Customers Also Bought



TE Part #2161700-5
5K CE STRIPPING MODULE W/ CQM



TE Part #2150061-2
OCEAN_2.0_Applicator-E-110F170F-REA



TE Part #2266118-2
OCEAN_2.0_APPLICATIONER-S-069F0800A-RSA



TE Part #311292-000
TMS-RJS-RIBBON-4DSCE



TE Part #073937-000
D-SCE-2.5K-6.4-50-S1-4



TE Part #2-480435-3
187 FASTON HSG.,REC.,1 POS,BLACK



Documents

Product Drawings

TERMIFOIL 4,75 REINFORCED TIN PL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_136557-2_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_136557-2_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_136557-2_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English