

TROLLEY WITH FOLDING BACKREST



250 KG

Very robust trolley for intensive use

- The welded steel frame is reinforced from underneath and guarantees a very good resistance in time.
- Rounded corners at the front to prevent injury.
- Foldable backrest with sturdy joint, made of Ø 28 mm tube for a good grip.
- Riveted top made of 12 mm thick varnished medium, very resistant, does not crack or splinter despite repeated impacts. No risk of splintering.
- 2 fixed wheels + 2 swivel wheels with brakes. Complies with the EN 1757 standard.
- Ergonomic height.
- Optional: anti-slip rubber mat, bins, writing trays, antistatic wheels, ...
- Delivered assembled



Reference	Tray dimensions mm	Overall dimensions mm	Ø Wheels	Bandage	Weight
800 000 142	1210 x 580	1280 x 630 x 960	125	CC	22

CC: rubber

PRODUCT ZOOM



OPTIONS

WHEELS



Antistatic wheels
Ø 125 mm 802 000 485
Polyurethane bandage to avoid any
risk of sparks.

2 fixed + 2 swivel with brake.



4 castor wheels
Ø 125 mm 802 010 590
Replacement of the 2 fixed wheels in
series by 2 swivel wheels.

4 castors, 2 of which have brakes.

ACCESSORIES



802 000 001
Door document
self-adhesive plastic



802 000 002
Wire basket



802 009 529
Document holder and
bottle



802 000 012
A4 standing document
holder



802 000 010
A3 coated document
holder

OTHER MODELS AVAILABLE



Tray 1000 x 560 mm,
CU 250 kg



Tray 1000 x 560 mm,
CU 400 kg