


### **FEATURES**

- Superior flexibility
- Resistant to a wide range of chemicals
- Silicone-free
- RoSH compliant
- High impact resistance

# RS PRO Air Hose Natural Nylon 8mm x 30m NMSF Series

RS Stock No.: 386-6229



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



# **Product Description**

Brought to you by RS Pro, a range of air hoses, ideal for the transfer or air, gas or fluid. Both Type 11 and Type 12 versions are available, providing solutions for areas requiring low toxic and food safe equipment (type 11). And also the more standard hose, which is perfect for various environments. All models are highly reliable and excellent quality.

#### **General Specifications**

| Colour           | Natural  |
|------------------|--|
| Material         | Nylon  |
| Number Of Tubes  | 1  |
| Special Features | Highly Flexible  |
| Application      | Air Brake, Fuel & Lube Applications, Industrial & Automotive Production Lines, Instrumentation & Secondary Air Systems |

## **Mechanical Specifications**

| Hose Inside Diameter  | 5.5mm |
|-----------------------|-------|
| Hose Outside Diameter | 8mm   |
| Length                | 30m   |

#### **Operation Environment Specifications**

| Maximum Operating Pressure    | 13.5 bar |
|-------------------------------|----------|
| Minimum Operating Temperature | -40°C    |
| Maximum Operating Temperature | +80°C    |





| Product     | Str       | te   | Min.<br>Bend | Burst<br>Pressure |     |
|-------------|-----------|------|--------------|-------------------|-----|
| Ref.        | I.D.      | Q.D. | Radius       | PS                | BAR |
| FLEXIBLEMED | DIUM GAUG | E    |              |                   |     |
| NMSF06      | .117      | 3/16 | 3/4          | 650               | 44  |
| NMSF08      | .170      | 1/4  | 11           | 650               | 44  |
| NMSF10      | .212      | 5/16 | 1 1/2        | 650               | 44  |
| NMFS12/SF   | .265      | 3/8  | 2            | 650               | 44  |
| NMSF12      | .250      | 3/8  | 2 1/2        | 650               | 44  |
| NMSF16      | .375      | 1/2  | 3            | 650               | 44  |



STOCK SIZES - METRIC

| Product 0   | Size   |        |      | Nominal<br>Wall<br>Thickness | Nom. Burst<br>Pressure<br>@ +20°C |     | Bend<br>Radius |
|-------------|--------|--------|------|------------------------------|-----------------------------------|-----|----------------|
|             | OD     | Tol.   | I.D. | mm                           | PSJ.                              | BAR | mm.            |
| FLEXIBLE ME | EDILMO | AUGE   |      | ,                            |                                   |     |                |
|             |        | +0.05/ |      |                              |                                   |     |                |
| NMSF04M     | 4      | -0.07  | 2.5  | 0.75±0.08                    | 917                               | 62  | 25mm           |
|             |        | +0.05/ |      |                              |                                   |     |                |
| NMSF05M     | 5      | -0.07  | 3.3  | 085±008                      | 850                               | 58  | 30mm           |
|             |        | +0.05/ |      |                              |                                   |     |                |
| NMSF06M     | 6      | -0.10  | 4    | 1.00 ± 0.08                  | B40                               | 57  | 35mm           |
|             |        | +0.05/ |      |                              |                                   |     |                |
| NMSF08M     | 8      | -0.10  | 5.5  | $1.25 \pm 0.08$              | 802                               | 55  | 45mm           |
|             |        | +0.05/ |      |                              |                                   |     |                |
| NMSF10M     | 10     | -0.10  | 7    | 1.50 ± 0.08                  | 773                               | 53  | 60mm           |
|             |        | +0.05/ |      |                              |                                   |     |                |
| NMSF12M     | 12     | -0.10  | 8.5  | 1.75 ± 0.08                  | 755                               | 51  | 70mm           |

| PHYSICAL PROPERTIES                          | METHOD                     | UNIT               |                 |  |
|--|----------------------------|--------------------|-----------------|--|
| Melting Point Range                          | Polarisation Microscope    | °C                 | 162 - 170       |  |
| Density                                      | DIN 53479                  | 9/cm3              | 1.05            |  |
| Water Absorption                             | Condition at 65% RH & 20°C | 96                 | 1.4             |  |
| Water Saturation                             | Condition at 85% RH & 20°C | Kp/cm2             | 160             |  |
| Tensile Strength, yield                      | DIN 53455                  | Kp/cm2             | 280             |  |
| Elongation at yield                          | DIN 53455                  | %                  | 350             |  |
| Tensile Strength at break                    | DIN 53455                  |                    |                 |  |
| Elongation at break                          | DIN 53455                  | Kp/cm2             | 140             |  |
| Flexural Strength at conventional deflection | DIN 53452                  | Kp/cm2<br>cmkp/cm2 | 210<br>No break |  |
| Ball Indentation hardness                    | VDE 0303 . 60 sec          |                    | 51              |  |
| Impact Strength                              | DIN 53453                  |                    |                 |  |
| Shore Hardness - Scale D                     |                            |                    |                 |  |