

Basic features

Approval/Conformity	CE UKCA WEEE
Function	Output converter (PNP/NPN) Switching inverter (NO/NC) Switching amplifier up to 150 mA
Use	for S4, switching output on pin 4

Electrical connection

Connection	M12x1
Connection slots	M12x1-Female, 4-pin

Electrical data

Current consumption without load, max.	10 mA
Input frequency max.	10000 Hz
Input resistance	≥ 10 kOhm
Operating voltage U_b	10...30 VDC
Protection class	II
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	150 mA
Residual ripple max.	2.4 Vpp

Remarks

For additional information, refer to user's guide.
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Environmental conditions

Ambient temperature	0...60 °C
IP rating	IP67
Storage temperature	-20...60 °C

Functional safety

MTTF (40 °C)	895 a
--------------	-------

Interface

Digital inputs	NPN
Duration of time function	1...65535 ms
Switching output	PNP normally open/normally closed (NO/NC)


Material

Housing material	PBT PA
------------------	-----------

Mechanical data

Dimension	Ø 20 x 60 mm
Mounting part	Union nut M12x1

Connector Drawings



Wiring Diagrams (Schematic)

