



**Part Number: 7962A**

DataTuff® 5e, 2 Pr #22 Str TC, PO Ins, OS+TC Brd, TPE Jkt, CM CMX-Outdoor

[Request Sample](#)

**Product Description**

Industrial Ethernet Cat 5e, 2 Pair 22AWG (19x34) Tinned Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(85%) Shield, TPE Outer Jacket, CM CMX-Outdoor

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor
Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, Category 5e, ProfiNet, 100BaseTX, CMX - Outdoor, PLTC Listed, Approved for Cable Tray Use in Class 1, Division 2, Hazardous Areas and Non-hazardous Areas, Cable Trays, Raceways, Conduit and Supported by Messenger Wires, Approved for Outdoor Usage

**Physical Characteristics (Overall)**

**Conductor**

Stranding	Material
19x34	TC - Tinned Copper

Total Number of Pairs:	2
Conductor Size:	22 AWG

**Insulation**

Material
PO - Polyolefin

**Inner Jacket Material**

Material	Nominal Diameter
FRPE - Flame Retardant Polyethylene	0.164 mm

**Outer Shield Material**

Type	Material	Material Trade Name	Coverage [%]
Tape	Aluminum/Polyester	Beldfoil®	100 %
Braid	TC - Tinned Copper		85 %

**Outer Jacket Material**

Material	Nominal Diameter
Industrial Grade TPE - Thermoplastic Elastomer	0.272 in

**Electrical Characteristics**

**Conductor DCR**

Max. Conductor DCR	Max. DCR Unbalance
5.7 Ohm/1000ft	3 %

**Capacitance**

Max. Capacitance Unbalance	Nom.Mutual Capacitance
150 pF/ft	15 pF/ft

**Delay**

Max. Delay	Nominal Velocity of Propagation (VP) [%]
------------	--

552 ns/100m 70 %

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.1 dB/100m	65.3 dB	62.3 dB	63.2 dB	63.8 dB	60.8 dB	23 dB	100 ± 20.2 Ohm	105 ±10 Ohm
4 MHz	4.0 dB/100m	56.3 dB	53.3 dB	56.3 dB	51.7 dB	48.7 dB	23 dB	100 ± 14.2 Ohm	100 ±10 Ohm
8 MHz	5.6 dB/100m	51.8 dB	48.8 dB	46.2 dB	45.7 dB	42.7 dB	23 dB	100 ± 11.3 Ohm	100 ±10 Ohm
10 MHz	6.3 dB/100m	50.3 dB	47.3 dB	43.9 dB	43.8 dB	40.8 dB	25 dB	100 ± 11.3 Ohm	100 ±10 Ohm
16 MHz	8.0 dB/100m	47.3 dB	44.3 dB	35.2 dB	39.7 dB	36.7 dB	25 dB	100 ± 11.3 Ohm	100 ±10 Ohm
20 MHz	9.0 dB/100m	45.8 dB	42.8 dB	36.5 dB	37.7 dB	34.7 dB	25 dB	100 ± 11.3 Ohm	100 ±10 Ohm
25 MHz	10.1 dB/100m	44.3 dB	41.3 dB	34.2 dB	35.8 dB	32.8 dB	25.5 dB	100 ± 11.3 Ohm	100 ±10 Ohm
31.25 MHz	11.4 dB/100m	42.9 dB	39.9 dB	31.3 dB	33.9 dB	30.9 dB	23.6 dB	100 ± 13.2 Ohm	100 ±10 Ohm
62.5 MHz	16.5 dB/100m	38.4 dB	35.4 dB	21.6 dB	27.8 dB	24.8 dB	21.5 dB	100 ± 16.9 Ohm	100 ±10 Ohm
100 MHz	21.3 dB/100m	35.3 dB	32.3 dB	17.1 dB	23.8 dB	20.8 dB	20.1 dB	100 ± 20.0 Ohm	100 ±10 Ohm

#### Voltage

<b>UL Voltage Rating</b>
600V

#### Temperature Range

Installation Temp Range:	-20°C To +60°C
UL Temp Rating:	75°C
Storage Temp Range:	-40°C To +80°C
Operating Temp Range:	-40°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	46 lbs/1000ft
Max Recommended Pulling Tension:	55 lbs
Min Bend Radius/Minor Axis:	2.560 in

#### Standards

NEC/(UL) Specification:	CMG, CMX-Outdoor, ITC, PLTC
CEC/C(UL) Specification:	CMG
ISO/IEC Compliance:	ISO/IEC 11801 Ed. 2.0:2002/A2:2010/C1:2011
Telecommunications Standards:	NEMA WC-63.1 Category 5e
Other Specification:	Oil Res II, Oil Res 60811-2-1, Weldsplatter Resistant

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2015/863/EU:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

#### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 Vertical Tray Flame Test
CSA Flammability:	FT4

IEEE Flammability:	1202
UL voltage rating:	600 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color
7962A.00305	Green
7962A.00610	Green
7962A 1SW1000	Green, RAL 6018
7962A 1SW2000	Green, RAL 6018

Patent:	<a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a>
---------	---

## Product Notes

Notes:	Operating Temperature subject to length de-rating. Cable passes -40C Cold Bend per UL 1581. Limits below 4 MHz are for information only.
--------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.