

SIMATIC S7,
 TD 200 TEXT DISPLAY FOR S7-200,
 2 LINES,
 WITH CABLE (2.5M) AND MOUNTING ACCESSORIES,
 CONFIGURATION WITH STEP7-MICROWIN



Operator control and monitoring

Operating / fault messages

Number of lines	2
Number of characters per line	20 ; Characters/line: ASCII, cyrillic; 10 characters/line: Chinese
Character size	5 mm

Display

Design of display	LCD backlit
--------------------------	-------------

Supply voltage

Rated voltage/DC	24 V ; Power supply via the S7-200 communications interface or optional external power supply unit; the CPU sensor power supply (24 V DC) is not subjected to load
-------------------------	--

Input current

Rated value at 24 V DC	120 mA
-------------------------------	--------

Interfaces

Point-to-point

Transmission rate (PPI), max.	187.5 kbit/s
--------------------------------------	--------------

1st interface

Physics	RS 485
----------------	--------

Functionality

PPI	Yes
PPI	
Number of nodes, max.	126 ; S7-200, OP, TP, TBP, PG/PC
Degree and class of protection	
IP65	Yes ; at front
Ambient conditions	
Operating temperature	
Min.	0 °C
max.	60 °C
Storage/transport temperature	
Min.	-40 °C
max.	70 °C
Dimensions	
Width	148 mm
Height	76 mm
Depth	27 mm
Mounting cutout (W x H x D)	
Mounting cutout, width	138 mm
Mounting cutout, height	68 mm
Cabinet/switchboard strength	0.3 mm ; 0.3 to 4 mm
Weight	
Weight, approx.	250 g
Status	Jul 22, 2013