



**06110045**

RCK 11 - Self centring

**2D Technical Drawing**

**Dynamic 3D View**

**Technical Specifications**

Part number (CODE)	06110045
Ød (DD) mm	45
ØD (D) mm	75
L1 (L1) mm	44
L2 (L2) mm	54
L (L) mm	62
Maximum torque Mt (MT) N/mm <sup>2</sup>	3240
Clamping pressure - Shaft (CPS) N/mm <sup>2</sup>	250
Clamping pressure - Hub (CPH)	150
Clamping pressure - N° (CPN)	7
Clamping screws DIN 912 MAT. 12.9 - Type (CSTY) mm	M8x50
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTO)	41
Extraction thread - Type (ETT) mm	M8
Extraction thread - N° (ETN)	3
Weight (WEIGHT) kg	0.90