

### Surface Mount Type

Series: **HB** Type: **V**

HB High temperature Lead-Free reflow (suffix:A\*)



#### ■ Features


- Endurance: 105 °C 2000 h
- Vibration-proof product is available upon request. ( $\phi 8 \leq$ )
- RoHS directive compliant

#### ■ Specifications

Category Temp. Range	-40 °C to +105 °C								
Rated W.V. Range	6.3 V.DC to 50 V.DC								
Nominal Cap. Range	0.1 $\mu$ F to 1500 $\mu$ F								
Capacitance Tolerance	$\pm 20$ % (120 Hz/ +20 °C)								
DC Leakage Current	$I \leq 0.01 CV$ or 3 ( $\mu$ A) After 2 minutes (Whichever is greater)								
$\tan \delta$	Please see the attached High temperature lead-free reflow products list.								
Characteristics at Low Temperature	Standard	W.V.(V)	6.3	10	16	25	35	50	(Impedance ratio at 120 Hz)
		Z(-25 °C)/Z(+20 °C)	4	3	2	2	2	2	
	Miniaturization product	Z(-25 °C)/Z(+21 °C)	4	3	2	2	2	2	
		Z(-40 °C)/Z(+21 °C)	10	8	6	6	4	4	
Endurance	After applying rated working voltage for 2000 hours at +105 °C $\pm 2$ °C and then being stabilized at +20 °C, capacitors shall meet the following limits.								
	Capacitance change	$\pm 20$ % of initial measured value (16 V.DC or less : Within $\pm 25$ %, Miniaturization product : Within $\pm 35$ %)							
	$\tan \delta$	$\leq 200$ % of initial specified value							
	DC leakage current	$\leq$ initial specified value							
Shelf Life	After storage for 1000 hours at +105 °C $\pm 2$ °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance. (With voltage treatment)								
Resistance to Soldering Heat	After reflow soldering and then being stabilized at +20 °C, capacitors shall meet the following limits.								
	Capacitance change	$\pm 10$ % of initial measured value							
	$\tan \delta$	$\leq$ initial specified value							
	DC leakage current	$\leq$ initial specified value							

#### ■ Marking


Example : 6.3 V 22  $\mu$ F (Polarized)  
Marking color : BLACK



##### Rated Voltage Mark

j	6.3 V
A	10 V
C	16 V
E	25 V
V	35 V
H	50 V

#### ■ Dimensions in mm (not to scale)



Size code	D	L	A,B	H max.	I	W	P	K
B	4.0	5.8	4.3	5.5	1.8	0.65 $\pm 0.1$	1.0	0.35-0.20 to +0.15
C	5.0	5.8	5.3	6.5	2.2	0.65 $\pm 0.1$	1.5	0.35-0.20 to +0.15
D	6.3	5.8	6.6	7.8	2.6	0.65 $\pm 0.1$	1.8	0.35-0.20 to +0.15
D8	6.3	7.7	6.6	7.8	2.6	0.65 $\pm 0.1$	1.8	0.35-0.20 to +0.15
E	8.0	6.2	8.3	9.5	3.4	0.65 $\pm 0.1$	2.2	0.35-0.20 to +0.15
F	8.0	10.2	8.3	10.0	3.4	0.90 $\pm 0.2$	3.1	0.70 $\pm 0.2$
G	10.0	10.2	10.3	12.0	3.5	0.90 $\pm 0.2$	4.6	0.70 $\pm 0.2$

**NEW**

■ High temperate Lead-Free reflow Products

Endurance : 105 °C 2000 h

W.V. (V)	Cap. (±20 %) (μF)	Case size			Specification		Part No. (RoHS:compliant)	Reflow	Min. Packaging Q'ty	
		Dia. (mm)	Length (mm)	*Size Code	Ripple Current (120 Hz) (+105°C) (mA r.m.s.)	tan δ (120 Hz) (+20 °C)			Taping (pcs)	
6.3	22	4	5.8	B	26	0.30	EEEHBOJ220AR	(5)	2000	
	33	4	5.8	B	29	0.30	EEEHBOJ330AR	(5)	2000	
	47	4	5.8	(B)	26	0.50	EEEHBJ470UAR	(5)	2000	
		5	5.8	C	46	0.30	EEEHBOJ470AR	(5)	1000	
	100	5	5.8	(C)	42	0.50	EEEHBJ101UAR	(5)	1000	
		6.3	5.8	D	71	0.30	EEEHBOJ101AP	(5)	1000	
	220	6.3	5.8	(D)	80	0.50	EEEHBJ221UAP	(5)	1000	
		8	10.2	F	150	0.35	EEEHBOJ221AP	(7)	500	
	330	8	6.2	(E)	180	0.50	EEEHBJ331UAP	(7)	1000	
		8	10.2	F	230	0.35	EEEHBOJ331AP	(7)	500	
470	8	10.2	(F)	230	0.50	EEEHBJ471UAP	(7)	500		
1500	10	10.2	(G)	290	0.50	EEEHBJ152UAP	(7)	500		
10	33	4	5.8	(B)	23	0.30	EEEHBA330UAR	(5)	2000	
		5	5.8	C	43	0.26	EEEHB1A330AR	(5)	1000	
	68	6.3	5.8	D	70	0.22	EEEHB1A680AP	(5)	1000	
	100	6.3	5.8	(D)	71	0.30	EEEHBA101UAP	(5)	1000	
		8	6.2	E	110	0.26	EEEHB1A101AP	(7)	1000	
	150	6.3	5.8	(D)	64	0.50	EEEHBA151UAP	(5)	1000	
	220	8	6.2	(E)	110	0.30	EEEHBA221UAP	(7)	1000	
		8	10.2	F	160	0.26	EEEHB1A221AP	(7)	500	
	470	8	10.2	(F)	220	0.35	EEEHBA471UAP	(7)	500	
		10	10.2	G	270	0.26	EEEHB1A471AP	(7)	500	
16	10	4	5.8	B	28	0.16	EEEHB1C100AR	(5)	2000	
	22	4	5.8	(B)	29.5	0.26	EEEHBC220UAR	(5)	2000	
		5	5.8	C	39	0.16	EEEHB1C220AR	(5)	1000	
	33	6.3	5.8	D	65	0.16	EEEHB1C330AP	(5)	1000	
		5	5.8	(C)	39	0.26	EEEHBC470UAR	(5)	1000	
	47	6.3	5.8	D	70	0.16	EEEHB1C470AP	(5)	1000	
		6.3	7.7	D8	84	0.16	EEEHBC470XAP	(5)	900	
	100	6.3	5.8	(D)	70	0.26	EEEHBC101UAP	(5)	1000	
		8	10.2	F	120	0.20	EEEHB1C101AP	(7)	500	
	220	8	10.2	(F)	150	0.20	EEEHBC221UAP	(7)	500	
10		10.2	G	210	0.20	EEEHB1C221AP	(7)	500		
330	10	10.2	G	230	0.20	EEEHB1C331AP	(7)	500		
470	8	10.2	(F)	240	0.40	EEEHBC471UAP	(7)	500		
	10	10.2	G	340	0.20	EEEHB1C471AP	(7)	500		
25	4.7	4	5.8	B	22	0.14	EEEHB1E4R7AR	(5)	2000	
	6.8	4	5.8	B	25	0.14	EEEHB1E6R8AR	(5)	2000	
	10	4	5.8	(B)	28	0.16	EEEHBE100UAR	(5)	2000	
		5	5.8	C	28	0.14	EEEHB1E100AR	(5)	1000	
	22	6.3	5.8	D	55	0.14	EEEHB1E220AP	(5)	1000	
	33	5	5.8	(C)	50	0.20	EEEHBE330UAR	(5)	1000	
		6.3	5.8	D	65	0.14	EEEHB1E330AP	(5)	1000	
	47	6.3	5.8	(D)	65	0.20	EEEHBE470UAR	(5)	1000	
		8	6.2	E	91	0.16	EEEHB1E470AP	(7)	1000	
	100	8	6.2	(E)	100	0.16	EEEHBE101UAP	(7)	1000	
8		10.2	F	130	0.16	EEEHB1E101AP	(7)	500		
220	8	10.2	(F)	130	0.30	EEEHBE221UAP	(7)	500		
	10	10.2	G	190	0.16	EEEHB1E221AP	(7)	500		
330	8	10.2	(F)	130	0.30	EEEHBE331UAP	(7)	500		
	10	10.2	G	220	0.16	EEEHB1E331AP	(7)	500		
470	10	10.2	(G)	230	0.30	EEEHBE471UAP	(7)	500		

\*Size code( ):Miniaturization product

If Part number exceeds 12 digits, voltage code is abbreviated as follows; 0J→J, 1A→A, 1C→C, 1E→E, 1V→V

The taping dimensions are explained on p.177 of our Catalog. Please use it as a reference guide.

Reflow Profile (Fig-1 to Fig-6) listed on p.175 of our Catalog.

■ High temperate Lead-Free reflow Products

Endurance : 105 °C 2000 h

W.V. (V)	Cap. (±20 %) (μF)	Case size			Specification		Part No. (RoHS:compliant)	Reflow	Min. Packaging Q'ty	
		Dia. (mm)	Length (mm)	*Size Code	Ripple Current (120 Hz) (+105°C) (mA r.m.s.)	tan δ (120 Hz) (+20 °C)			Taping (pcs)	
35	4.7	4	5.8	B	21	0.12	EEEHB1V4R7AR	(5)	2000	
	6.8	4	5.8	(B)	25	0.12	EEEHBV6R8UAR	(5)	2000	
	10	5	5.8	C	28	0.12	EEEHB1V100AR	(5)	1000	
	22	6.3	5.8	D	55	0.12	EEEHB1V220AP	(5)	1000	
	33	8	6.2	E	84	0.14	EEEHB1V330AP	(7)	1000	
	47	6.3	7.7	D8	98	0.20	EEEHBV470YAP	(5)	900	
		8	6.2	(E)	91	0.18	EEEHBV470UAP	(7)	1000	
		8	10.2	F	98	0.14	EEEHB1V470AP	(7)	500	
	100	8	10.2	(F)	98	0.20	EEEHBV101UAP	(7)	500	
		10	10.2	G	160	0.14	EEEHB1V101AP	(7)	500	
220	10	10.2	(G)	180	0.14	EEEHBV221UAP	(7)	500		
50	0.1	4	5.8	B	1	0.12	EEEHB1HR10AR	(5)	2000	
	0.22	4	5.8	B	2	0.12	EEEHB1HR22AR	(5)	2000	
	0.33	4	5.8	B	3	0.12	EEEHB1HR33AR	(5)	2000	
	0.47	4	5.8	B	5	0.12	EEEHB1HR47AR	(5)	2000	
	0.68	4	5.8	B	7	0.12	EEEHB1HR68AR	(5)	2000	
	1	4	5.8	B	10	0.12	EEEHB1H1R0AR	(5)	2000	
	2.2	4	5.8	B	16	0.12	EEEHB1H2R2AR	(5)	2000	
	3.3	4	5.8	B	16	0.12	EEEHB1H3R3AR	(5)	2000	
	4.7	5	5.8	C	23	0.12	EEEHB1H4R7AR	(5)	1000	
	6.8	5	5.8	C	23	0.12	EEEHB1H6R8AR	(5)	1000	
	10	6.3	5.8	D	35	0.12	EEEHB1H100AP	(5)	1000	
	22	6.3	5.8	(D)	35	0.14	EEEHBH220UAP	(5)	1000	
		8	6.2	E	70	0.12	EEEHB1H220AP	(7)	1000	
	33	8	10.2	F	91	0.12	EEEHB1H330AP	(7)	500	
	47	6.3	7.7	D8	63	0.12	EEEHBH470YAP	(5)	900	
8		10.2	(F)	95	0.12	EEEHBH470UAP	(7)	500		
10		10.2	G	100	0.12	EEEHB1H470AP	(7)	500		
100	10	10.2	(G)	250	0.12	EEEHBH101UAP	(7)	500		
220	10	10.2	(G)	150	0.18	EEEHBH221UAP	(7)	500		

\*Size code( ):Miniaturization product

If Part number exceeds 12 digits, voltage code is abbreviated as follows; 0J→J, 1A→A, 1C→C, 1E→E, 1V→V

The taping dimensions are explained on p.177 of our Catalog. Please use it as a reference guide.

Reflow Profile (Fig-1 to Fig-6) listed on p.175 of our Catalog.