




Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Cavity Diameter: **2 mm [.08 in]**

Primary Product Color: **Gray**

Primary Product Material: **Silicone Rubber**

Compatible Insulation Diameter Range: **2.7 – 3 mm [.106 – .118 in]**

Contains Lubricant: **Yes**

Features

Body Features

Primary Product Color	Gray
Primary Product Material	Silicone Rubber

Dimensions

Cavity Diameter	2 mm[.08 in]
Compatible Insulation Diameter Range	2.7 – 3 mm[.106 – .118 in]

Other

Contains Lubricant	Yes
--------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 282956-7 SPLASH-PROOF FEM CONN ASSY	 TE Part # CAT-T4827-CH8172 Timer Connector Housing	 TE Part # 282729-2 SPLASH PROOF CONN. ASS'Y	 TE Part # 282194-2 SPLASH PROOF CONN. W.S.L.
 TE Part # 282762-3 JPT SPLASH-PROOF FEM.CONN2 POS	 TE Part # 282189-8 SPLASH PROOF CONN. W.S.L.	 TE Part # 2293416-1 ISO FUSE AND RELAY, 38 POSNUNSLD BASE	 TE Part # 2137216-2 3P SPLASH PROOF CONNECTOR ASS'
 TE Part # 282246-1 SPLASH PROOF FEMALE CONN:3 VIE	 TE Part # 1-1719504-1 TAB 2.8x0.8 CONTACT CS SWS Sn	 TE Part # CAT-AM7-FRB69 Sealed Fuse and Relay Boxes	 TE Part # 282788-3 SPLASH-PROOF CONN W.S.L. 2P TY



TE Part # 282648-1
SPLASH PROOF CONN. W.S.L.2 WAY

TE Part # 1-1719506-1
AMP MCP 2.8, CONTACT SWS

TE Part # 2137216-1
3P SPLASH PROOF CONNECTOR ASS'

Also in the Series

Junior Power Timer

Automotive Connector Caps & Covers (9)

Automotive Connector Locks & Position Assurance(8)

Automotive Housings(284)

Automotive Terminals(153)

Busbars & Terminals(1)

Connector Seals & Cavity Plugs(7)

Module Components(1)

Other Automotive Connector Accessories(2)

Special Purpose Terminals(2)

Customers Also Bought

TE Part #2098164-3
Cover, 60 Pos, No Top Side Fuse Graphic

TE Part #284443-4
COVER + LEVER FOR 12 POS M.Q.S

TE Part #2272006-2
Plug Assembly, 20P GET, w/ CPA

TE Part #CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB





TE Part #1745011-1

PANEL HOOK



TE Part #0021036002

RBK-ILS-125-NR3-0-50MM




TE Part #2360105-1

REC CONN CVR ASSY,112POS, HYBRID,180DEG

TE Part #570055-000

BL-POLY125-16-0-90MM



TE Part #1745044-2

24 POS MALE CONN.SEALED FOR TAB1.5/2.8

Documents

Product Drawings

S.WAY SEAL F.JPT CONTACT 2.5MM

English

CAD Files

Customer View Model

ENG_CVM_282536-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_282536-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_282536-1_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

15 AND 35 POS. SPLASH PROOF FEM. CONN. FOR J.P.T.

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

282536-1

2 mm [.08 in] Cavity Diameter, Gray, Silicone Rubber, 2.7 – 3 mm [.106 – .118 in]
Insulation Diameter, Junior Power Timer



10 & 20 Way Sealed Sectioning Connector

English