
## BES 516-325-E4-C-03 BES00P9





- PNP
- Normally open (NO)
- 2.00 mm
- Flush (shielded)
   Cable, PVC, 3.00 m









IND. CONT. EQ
81U2
US for use in the secondary of a class 2 source of supply
Environmental - Type 1 Enclosure



2.0 V

### General attributes Approvals / Conformity

cULus EAC Basic standard IEC 60947-5-2 Enclosure Type per IEC 60529 Function indicator IP68 according to BWN PR 20 Yes Polarity reversal protected Yes Power indicator No Protection Class Short circuit protected Yes

CE

830 a

# Electrical attributes

Switching output

MTTF

Connection type Eff. operating current le Eff. operating voltage Ue DC Electrical version Load capacitance max. (at Ue) Max. no-load cur. lo undamped Minimum operating current Im No-load current lo damped max. Operating voltage UB max. DC [V]
Operating voltage UB min. DC [V]
Rated insulation voltage Ui Rated short circuit current Ripple max. (% of Ue) Switching freq. f max. (at Ue) Switching function

Cable 200 mA 24.0 V DC, direct current 0.500  $\mu\text{F}$ 4.0 mÅ 0 mA 10.0 mA 30.0 V 10.0 V 250 VAC 100 A 15 %

5000 Hz Normally open (NO) PNP Voltage drop static max.

Mechanical attributes
Ambient temperature Ta max. 70 °C -25 °C 1.60 mm Ambient temperature Ta min. Assured operating distance Sa Cable diameter D max. 4.6 mm Cable jacket material PVC 3.00 m 0.34 mm<sup>2</sup> Cable length Conductor cross-section Depth 33.0 mm Diameter d1 M12x1 Eff. operating distance Sr 2.00 mm Housing material CuZn Flush (shielded) Mech. installation condition Mounting length 30.0 mm Number of conductors 3 2.00 mm Rated operating distance Sn [mm] Sensing face material PBT Surface protection Nickel-plated Tightening torque 15 Nm

The sensor is functional again after the overload has been eliminated.

For further information on MTTF/B10d, please refer to the MTTF / B10d Certificate.

Specification of the MTTF value and the B10d value do not represent any binding quality and/or life expectancy guarantees.

