




Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Conducting Accessories



Conducting Accessory Type: **Jumper Bar**
Number of Poles: **2**
PCB Mount Retention Type: **Screwless**
Primary Product Color: **Orange**
Product Spacing: **8 mm [.315 in]**

Features

Product Type Features

Conducting Accessory Type	Jumper Bar
---------------------------	------------

Configuration Features

Number of Poles	2
-----------------	---

Electrical Characteristics

Power Loss	1.8 W
Dielectric Withstanding Voltage (Max)	2200 V
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	600 V
Impulse Withstanding Voltage Rating (IEC)	6000 V
Current Rating (IEC)	57 A
Current Rating (UL)	42 A
Current Rating (CSA)	42 A
Voltage Rating (IEC)	1000 V
Voltage Rating (CSA)	600 V
Short-Time Withstanding Current Rating @ 1s	1200 A



Body Features

Plastic & Resin Material Type	Polyamide
Product Weight	2.7 g[.095 oz]
Primary Product Color	Orange

Contact Features

Contact Current Rating (Max)	57 A
------------------------------	------

Mechanical Attachment

PCB Mount Retention Type	Screwless
--------------------------	-----------

Dimensions

Product Width	8 mm[.315 in]
Product Depth	27.8 mm[1.094 in]
Product Height	13.6 mm[.535 in]
Product Spacing	8 mm[.315 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Industry Standards

IP Rating	IP20
-----------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>








EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1SNK708031R0000 ZK6-3P-OR	 TE Part # 1SNK708411R0000 ZK4-SF1-R1	 TE Part # 1SNK508066R0000 ZS10-BK	 TE Part # 1SNK708062R0000 ZK6-RD
 TE Part # 1SNK508063R0000 ZS10-PR	 TE Part # 1SNK508425R0000 ZS4-D2-SF1	 TE Part # 1SNK708020R0000 ZK6-BL	 TE Part # 1SNK508064R0000 ZS10-BR
 TE Part # 1SNK508061R0000 ZS10-GN	 TE Part # 1SNK508150R0000 ZS10-PE	 TE Part # 1SNK508424R0000 ZS4-D2-SF1-R3	 TE Part # 1SNK708010R0000 ZK6
 TE Part # 1SNK708060R0000 ZK6-YL	 TE Part # 1SNK708413R0000 ZK4-SF1-R3	 TE Part # 1SNK508423R0000 ZS4-D2-SF1-R1	 TE Part # 1SNK508065R0000 ZS10-WH

1SNK908302R0000


Jumper Bar, 2 Pole, Orange, 8 mm [.315 in] Spacing, -55 – 110 °C [-67 – 230 °F],
ENTRELEC SNK



TE Part # 1SNK508030R0000
[ZS10-OR](#)



TE Part # 1SNK708414R0000
[ZK4-S-R3](#)



TE Part # 1SNK708030R0000
[ZK6-OR](#)



TE Part # 1SNK708011R0000
[ZK6-3P](#)


Also in the Series | **ENTRELEC SNK**



[Modular Terminal Blocks\(319\)](#)




[Terminal Block & Strip Conducting Accessories\(67\)](#)



[Terminal Block & Strip Insulating Accessories\(31\)](#)


Customers Also Bought




TE Part #1SNK706411R0000
[ZK2.5-SF-R1](#)



TE Part #1SNK508066R0000
[ZS10-BK](#)



TE Part #1SNK508062R0000
[ZS10-RD](#)



TE Part #1SNK506310R0000
[ZS4-S-R1](#)



TE Part #1SNK900603R0000
[JB85-3](#)




TE Part #1SNK508065R0000
[ZS10-WH](#)




TE Part #1SNK908303R0000
[JB8-3](#)



TE Part #1SNK160000R0000
[MC812](#)



TE Part #1SNK705060R0000
[ZK2.5-YL](#)



TE Part #1SNK508010R0000
[ZS10](#)



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK908302R0000_C1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK908302R0000_C1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK908302R0000_C1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Blocks Catalogue (RUS)

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English

Essential Entrelec Terminal Blocks

French

Essential Entrelec Terminal Blocks

English

Essential Entrelec Terminal Blocks

Japanese