




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Wire-to-Wire**
Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	12
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

--	--



Contact Layout	Inline
Contact Type	Receptacle
Contact Retention Within Housing	Without

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	Nylon 66/6
Centerline (Pitch)	3 mm[.118 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CNR, USR
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476, VDE 40005280
CSA Rating	Certified, LR 7189
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)




Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1445087-2
MICRO MNL HDR ASSY S/ROW AU LF



TE Part # 3-1445091-2
MICRO MNL HDR ASSY S/ROW AU LF




TE Part # 2008570-4
4 POS MICRO MNL, SIDE LATCH, B



TE Part # 1-2008571-4
4 POS MICRO MNL, TOP LATCH, NA



TE Part # 1-2008571-2
2 POS MICRO MNL, TOP LATCH, NA



TE Part # 1-1445049-2
FREE HANG SNGL ROW HSG 12 POS



TE Part # 2008570-5
5 POS MICRO MNL, SIDE LATCH, B



TE Part # 1-1445048-2
PANEL MT SNGL ROW HSG 12 POS

Also in the Series | [Micro MATE-N-LOK](#)



Connector Contacts(27)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(371)




Power Contacts(27)



Rectangular Connector Housings(98)



Rectangular Power Connectors(469)



Wire-to-Board Headers & Receptacles (371)

Customers Also Bought



TE Part #5039924004
SRFR-2.9/1.7-8-SP



TE Part #1589693-1
OCM044PC2DC006B = CIRCULAR



TE Part #179518-1
CT CRIMP-2 REC CONT. L/P



TE Part #320553
PIDG R 22-16 COMM 22-18 MIL 4




TE Part #1-794617-4
14POS,MICRO MNL,RCPT HSG



TE Part #2-794617-0
20POS,MICRO MNL,RCPT HSG



TE Part #1-794610-1
MICRO MNL RPT CNT,LS PC 15AU L



TE Part #D17660-000
D-200-82



TE Part #YDTS20W21-35PNV001
RECP ASSY

TE Part #MS121-00000U-100PG
PRESS XDCCR MS121-00000U-100PG

Documents



Product Drawings

MICRO MNL RFECEPT HSG SINGLE R

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1445022-2_F1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1445022-2_F1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1445022-2_F1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

MICRO MATE-N-LOK CONNECTOR SYSTEM

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English