


Fiber optic cable - FOC-PT9:LC-OM1/2.5 - 1250833

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Fiber optic cable, degree of protection: IP20, cable length: 2.5 m, number of positions: 12, material: Plastic, connection method: LC, cable outlet: straight, color: beige



Your advantages

- ✔ Optimum attenuation values with UPC polishing
- ✔ Time saving and minimized risk of breakage with easy offsetting
- ✔ Easy assignment thanks to 12 different colors
- ✔ Future-proof with RoHS 2 conformity
- ✔ Fire protection class UL 94-V0



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4063151355166
Weight per Piece (excluding packing)	22.220 g
Custom tariff number	85447000
Sales Key	ABNACZ

Technical data

Dimensions

Length of cable	2.50 m
Width	5.5 mm
Height	9.7 mm
Length	2500 mm

Ambient conditions

Ambient temperature (assembly)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (operation)	-20 °C ... 70 °C

Fiber optic cable - FOC-PT9:LC-OM1/2.5 - 1250833

Technical data

General

Number of positions	12
Connection method	LC
Halogen-free	yes
Resistance to oil	no
Flame resistance	yes
Type	LC

Material

Flammability rating according to UL 94	V0
Housing material	Plastic

Cable

Cable structure	semi-loose compact wires (STB)
Outer sheath, material	LSZH
Flame resistance	yes
Halogen-free	yes
Resistance to oil	no

Standards and Regulations

Flame resistance	yes
Resistance to oil	no
Halogen-free	yes

Classifications

eCl@ss

eCl@ss 11.0	27060390
eCl@ss 9.0	27060390

ETIM

ETIM 7.0	EC000748
----------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Fiber optic cable - FOC-PT9:LC-OM1/2.5 - 1250833

Approvals

Approval details

EAC		B.01687
-----	---	---------