



tested to work



19279-510 Trousers with kneepad pockets

ULTIMATE STRETCH - water-repellent - two-toned - suitable for Industrial wash

MASCOT® ACCELERATE SAFE



83% recycled polyester/17% elastolefin

205 g/m²



ULTIMATE STRETCH. Shrinkage max. 2%. The product is certified to retain its qualities with 50 domestic washes or ≥ 25 industrial washes.

Industrial care category B1

CORDURA
F A B R I C

Certifications




EN ISO 20471



HIGH-VIS GROUP:



ProWash®



- Ultimate stretch material provides unique freedom of movement and high comfort.
- The water-repellent multifunctional stretch material combines a low weight with a very high durability.
- Ergonomically shaped trouser legs are constructed to follow the body's natural movements.
- Ruler pocket with Kevlar® reinforcement - particularly resistant to pointed and sharp objects.
- Prepared for holster pockets 19450-126, which are attached with buttons.
- Effective ventilation to the leg via the zip on the back of the thigh.
- The kneepad pockets of durable CORDURA® are adjustable so the kneepads have the optimal position on your knees.
- Co-certified for use with MASCOT kneepad type SHORT or LONG, as the kneepad pocket is height-adjustable.
- The product tolerates industrial washing.

Technical info

Fluorescent and with reflective tapes. The polyester is made from recycled resources. Has a water-repellent finish. Two-toned. Lightweight. Ultimate stretch fabric with extra low weight and high wear resistance. Double stitched seams on leg and crotch. Hidden stud fastening. Ergonomically formed trouser leg. Belt loops. Fly with zip. Front pockets. Back pockets with reinforcement. Hidden tool strap on right side. Ruler pocket with Kevlar® reinforcement. Thigh pockets with flaps. Adjustable kneepad pockets in very durable CORDURA® (1000 D). Thigh pocket with lined telephone pocket, hidden press stud fastening and integrated ID card holder. Detachable ID card holder. Vertical zip to allow for ventilation on back of thigh. With print effects. Prepared for holster

Logo

As the product is made of stretch material, a stretchable transfer must be used when printing on the product. You should choose a transfer that can be heated at a maximum of 145 degrees with consideration to print on the product. Remember to check the washing instructions for the chosen transfer before washing the product.

The product is certified with maximum (82+90 cm) 0,0300 m² (76 cm) 0,0400m² logo area. This approved area must not be exceeded. Logo on, respectively, front or back of the product can constitute only a maximum of 50% of the total approved logo area in order to maintain the EN ISO 20471-certification. Note: The listed area is only a guide to how much space is available for logo placement. In order to maintain the product's hi-vis class according to EN ISO 20471, the instructions on logo size must be observed.

Logo placement:

- Workwear logo. Over left front pocket. Max 11x6 cm/4.3x2.3 inches
- Workwear logo. Over right front pocket. Max 11x6 cm/4.3x2.3 inches
- Workwear logo stretch. Left back pocket. Max 11x4 cm/4.3x1.5 inches
- Workwear logo stretch. Right back pocket. Max 11x4 cm/4.3x1.5 inches
- Workwear logo stretch. Horizontal on right thigh. Max 9x6 cm/3.5x2.3 inches

pockets 19450-126, which are attached with buttons. Each standard leg length can be lengthened by 3 cm by releasing the internal red stitches. We recommend 00418-100, 00718-100, 50454-916 & 20118-915 kneepads for this model. Co-certified together with kneepad type SHORT or LONG in accordance with EN 14404.

User

