



PRODUCT-DETAILS

AF26-22-00-13

AF26-22-00-13 100-250V50/60HZ-DC

Contactors



概要信息	
产品型号	AF26-22-00-13
产品ID	1SBL237501R1300
欧洲商品编号(EAN)	3471523116436
目录说明	AF26-22-00-13 100-250V50/60HZ-DC Contactor
详细描述	The AF26-22-00-13 is a 4 pole - 690 V IEC or 600 UL contactor with screw terminals, controlling motors up to 11 kW / 400 V AC (AC-3) and switching power circuits up to 45 A (AC-1) or 45 A UL general use. Thanks to the AF technology, the contactor has a wide control voltage range (100-250 V 50/60 Hz and DC), managing large control voltage variations, reducing panel energy consumptions and ensuring distinct operations in unstable networks. Furthermore, surge protection is built-in, offering a compact solution. AF contactors have a block type design, can be easily extended with add-on auxiliary contact blocks and an additional wide range of accessories.

订货信息	
最小起订量	1 piece

Popular Downloads

数据手册，技术资料	1SBC100214C0202
说明书和手册	1SBC101027M6801
CAD Dimensional Drawing	2CDC001079B0201

尺寸

产品净宽	45 mm
产品净深	101 mm
产品净高	86 mm
产品净重	0.36 kg

技术参数

主触点NO数量	2
主触点NC数量	2
辅助触点NO数量	0
辅助触点NC数量	0
标准	IEC/EN 60947-1, IEC/EN 60947-4-1, UL 60947-1, UL 60947-4-1, CAN/CSA C22.2 No.60947-1, CAN/CSA C22.2 No.60947-4-1
额定工作电压	Main Circuit 690 V
额定频率 (f)	Control Circuit 50 / 60 Hz Main Circuit 50 / 60 Hz
额定发热电流（自由空气）(I _{th})	acc. to IEC 60947-4-1, Open Contactors Θ = 40 °C 55 A
额定工作电流 AC-1 (I _e)	(690 V) 40 °C 45 A (690 V) 60 °C 40 A (690 V) 70 °C 32 A
额定工作电流 AC-3 (I _e)	(415 V) 60 °C 21.2 A (440 V) 60 °C 20 A (500 V) 60 °C 17.6 A (690 V) 60 °C 10.5 A (380 / 400 V) 60 °C 22 A (220 / 230 / 240 V) 60 °C 23.2 A
额定工作功率 AC-3 (P _e)	(400 V) 11 kW (415 V) 11 kW (440 V) 11 kW (500 V) 11 kW (690 V) 9 kW (220 / 230 / 240 V) 5.5 kW
额定不间断电流 (I _{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 300 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 55 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 150 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 450 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 225 A
最高电气切换频率	(AC-1) 600 cycles per hour
额定绝缘电压 (U _i)	acc. to IEC 60947-4-1 690 V acc. to UL/CSA 600 V
额定冲击耐受电压 (U _{imp})	6 kV
最高机械切换频率	3600 cycles per hour
额定控制电路电压 (U _c)	50 Hz 100 ... 250 V 60 Hz 100 ... 250 V DC Operation 100 ... 250 V
工作时间	Between Coil De-energization and NC Contact Closing 13 ... 98 ms Between Coil De-energization and NO Contact Opening 11 ... 95 ms Between Coil Energization and NC Contact Opening 38 ... 90 ms Between Coil Energization and NO Contact Closing 40 ... 95 ms
安装到DIN导轨上	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715

螺钉安装（螺钉须自备）	2 x M4 screws placed diagonally
主电路连接容量	Flexible with Ferrule 1/2x 1.5 ... 16 mm ² Flexible with Insulated Ferrule 1/2x 1.5 ... 16 mm ² Rigid Solid 1/2x 1.5 ... 4 mm ² Rigid Stranded 1/2x 1.5 ... 16 mm ²
控制电路连接容量	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Rigid Solid 1/2x 1 ... 2.5 mm ² Rigid Stranded 1/2x 1 ... 2.5 mm ²
剥线长度	Control Circuit 10 mm Main Circuit 12 mm
防护等级	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
端子类型	Screw Terminals

UL/CSA适用的技术参数

最高工作电压UL/CSA	Main Circuit 600 V
通用等级UL/CSA	(600 V AC) 45 A
主电路连接容量 UL/CSA	Rigid Solid 1/2x 16-10 AWG Rigid Stranded 1/2x 16-6 AWG
控制电路连接容量 UL/CSA	Rigid Solid 1/2x 18-14 AWG Rigid Stranded 1/2x 18-14 AWG
拧紧力矩UL/CSA	Control Circuit 11 in-lb Main Circuit 22 in-lb

环境条件

周围环境温度	Close to Contactor for Storage -60 ... +80 °C Near Contactor for Operation in Free Air -40 ... 70 °C
耐候	Category B according to IEC 60947-1 Annex Q
允许的最高工作海拔	Without Derating 3000 m
抗机械冲击符合IEC 60068-2-27标准	Closed, Shock Direction: A 30 g Closed, Shock Direction: B1 25 g Closed, Shock Direction: B2 15 g Closed, Shock Direction: C1 25 g Closed, Shock Direction: C2 25 g Open, Shock Direction: A 25 g Open, Shock Direction: B1 5 g Open, Shock Direction: B2 10 g Open, Shock Direction: C1 20 g Open, Shock Direction: C2 20 g
耐振动符合IEC 60068-2-6 标准	4g Closed Position & 2g Open position 5 ... 300 Hz

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS信息	2CMT2021-006277
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

ABB EcoSolutions	
产品环境声明 - EPD	1SBD250584E4000
产品中可持续材料含量 (重量%)	Recycled Metal - 28 %
包装中的可持续材料含量 (重量%)	Recycled Cardboard - 86 %
产品寿命终止后的拆解指南	1SBC101080M6801

认证及声明（文件编码）	
ABS认证	ABS_20-2060694-PDA
CB认证	SE-113783
CCC认证	CCC_2010010304445623
CQC认证	CQC2010010304445623 CQC2020010304294316
Declaration of Conformity - CCC	2020980304001254 2020980304001052
符合性声明 - CE	1SBD250001U1000
Declaration of Conformity - UKCA	1SBD250032U1000
DNV认证	DNV_TAE00001AF-4
GOST认证	GOST_POCCFR.ME77.B07175.pdf
KC认证	KC_HW02016-15002C
LR认证	LRS_LR23403517TA-02
RINA认证	RINA_ELE084013XG
RMRS认证	RMRS_1802705280
UL认证	UL-US-L319322-13-72119002-5 UL-CA-L319322-43-72119002-6
UL列表卡	UL_E319322

包装信息	
1级包装单元	box 1 piece
1级包装宽度	87 mm
1级包装长度	103 mm
1级包装高度	47 mm
1级包装 总重	0.36 kg
1级包装 EAN	3471523116436
2级包装单元	box 18 piece
2级包装宽度	250 mm
2级包装长度	300 mm
2级包装高度	315 mm
2级包装 总重	12.96 kg
3级包装单元	864 piece

分类	
对象分类代码	Q
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 8	EC000066 - Power contactor, AC switching
ETIM 9	EC000066 - Power contactor, AC switching
e级	V11.0 : 27371003

UNSPSC	39121529
IDEA 粒度分类代码 (IGCC)	4758 >> lec Contactors
E-Number (Finland)	3705846
E-Number (Sweden)	3211516

分类

低压产品及系统 → 控制产品 → 接触器 → 模块化接触器 → AF Contactors → AF26

