



Image may differ from product. See technical specification for details.

TMBA G11ET

SKF Extreme Temperature Gloves TMBA G11ET

The TMBA G11ET gloves are especially designed for allowing the safe handling of heated bearings or other components for prolonged periods. They can withstand extreme temperatures of up to 400 °C (752 °F), without the presence of hot liquid or steam, with a high degree of non-flammability.

- Extremely tough KEVLAR® gloves with high cut, abrasion, puncture and tear resistance for increased safety
- Heat-resistance to extreme temperatures allows the safe and prolonged handling heated components
- High-degree of non-flammability reduces the risk of burning

- Comfortable to wear, as they are knitted from flexible high performance materials in one piece without seams
- Tested and certified for mechanical risks (EN 388) and thermal risks (EN 407)

Overview

Dimensions

Suitable for Hand size	10
------------------------	----

Performance

Use temperature (max.)	400 °C
Performance according EN 420: General requirements	Sizes 10
Performance according EN 388: Mechanical risks	Abrasion resistance: 2 Cut resistance (Coup): 5 Tear resistance: 4 Puncture resistance: 3 Cut resistance (TDM): F
Performance according EN 407: Thermal risks	Limited Flame Spread: 4 Contact heat: 4 Convective heat: 4 Radiant heat: 3 Small drops of molten metal: X Large drops of molten metal: X Removal of Gloves: Pass

Properties

Recommended applications	Heat resistant gloves specially designed for the handling of heated bearings or other components for prolonged periods
Oil and grease resistant	No
Suitable for submerging in liquids	No
Material, outer layer	Para-aramid
Material, middle layer	Para-aramid
Material, inner layer	Cotton
Special features	Non-allergenic
Washing	Not recommended
Colour	Yellow
Recommended storage temperature	5.0 – 25.0 °C
Content	1 pair

Logistics

Product net weight	0.31 kg
eClass code	23-05-19-01
UNSPSC code	40101831

Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.